

29mm BGA (Radial Heat Sinks)

Heat Sink Type	Heat Sink Diameter Inches (mm)	Heat Sink Height Inches (mm)	Power (W)	Thermal Resistance (°C/W) Theta ca				Assembly Part Numbers	
				0 LFM	200 LFM	400 LFM	600 LFM	3 Leg Low Profile Clip 1542432-1	3 Leg Standard Clip 1542816-1
2 Fin Radial	2.000 (50.80)	0.367 (9.32)	5 10 15	N/A				N/A	9-1542010-5
	2.25 (57.15)	0.350 (8.89)	5	8.71	4.55	2.98	2.37	6-1542007-1	1-1542009-4
			10	8.07	4.57	2.99	2.39		
15	7.50	4.53	2.99	2.39					
3 Fin Radial	1.375 (34.92)	0.479 (12.16)	5	13.25	6.13	4.35	3.14	7-1542004-0	1963201-1
			10	11.82	6.04	3.99	2.93		
			15	10.75	5.89	3.96	2.99		
	2.000 (50.80)	0.414 (10.51)	5	N/A				1542008-7	N/A
			10	N/A					
			15	N/A	4.20	2.79	2.26		
2.000 (50.80)	0.479 (12.16)	5	N/A				2-1542007-3	1542011-3	
		10	N/A						
		15	N/A	4.20	2.79	2.26			
4 Fin Radial	1.250 (31.75)	0.600 (15.24)	5	12.19	5.49	3.85	2.95	7-1542004-8	1542009-2
			10	11.04	5.47	3.76	2.82		
			15	10.07	5.35	3.67	2.82		
	1.375 (34.92)	0.591 (15.01)	5	12.59	5.39	3.28	2.8	2-1542007-2	N/A
			10	11.18	5.31	3.35	2.63		
			15	10.17	5.32	3.26	2.61		
2.000 (50.80)	0.591 (15.01)	5	8.75	3.80	2.30	2.13	2-1542007-4	6-1542010-6	
		10	7.87	3.79	2.20	1.89			
		15	7.37	3.69	2.19	1.88			
6 Fin Radial	1.500 (38.10)	0.787 (19.98)	5 10 15	N/A				5-1542008-2	3-1542009-6
	2.000 (50.80)	0.811 (20.60)	5	N/A				1-1542009-7	N/A
			10	N/A					
15	N/A								
7 Fin Radial	1.375 (34.92)	0.927 (23.54)	5	10.54	3.76	2.7	1.79	8-1542006-5	N/A
			10	9.61	3.73	2.42	2.01		
			15	8.79	3.73	2.36	1.93		
	2.000 (50.80)	0.892 (22.65)	5	N/A				5-1542007-9	9-1542011-4
			10	N/A					
20	N/A	1.56	1.36						

Please refer to customer drawing for torque and other specifications.