

49.5mm BGA (Radial Heat Sinks)

Heat Sink Type	Heat Sink Diameter Inches (mm)	Heat Sink Height Inches (mm)	Power (W)	Thermal Resistance (°C/W) Theta ca				Assembly Part Numbers
				0 LFM	200 LFM	400 LFM	600 LFM	With 2 Leg Clip 1542378-1
2 Fin Radial	3.000 (76.20)	0.433 (10.99)	5	5.69	3.08	2.04	1.75	6-1542004-2
			10	5.33	2.95	1.94	1.63	
			15	5.08	2.90	1.89	1.59	
3 Fin Radial	3.000 (76.20)	0.600 (15.24)	5	N/A				4-1542004-9
			10					
			15					
4 Fin Radial	3.000 (76.20)	0.770 (19.55)	5	N/A				4-1542004-8
			10					
			15					
6 Fin Radial	2.000 (50.80)	0.785 (19.93)	5	7.57	2.75	1.97	1.65	1542007-5
			10	6.99	2.92	1.78	1.49	
			15	6.51	2.76	1.74	1.43	
8 Fin Radial	2.000 (50.80)	1.500 (38.10)	5	6.50	N/A			1-1542000-8
			10	5.91				
			15	5.51				
9 Fin Radial	2.000 (50.80)	1.208 (30.68)	5	N/A				2-1542008-7
			10					
			15					

Please refer to customer drawing for torque and other specifications.