



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		A	REVISED PER ECO-11-022043	11NOV11	KH	PO

QTY	DESCRIPTION	ALCOSWITCH PART NUMBER	PART NUMBER
1	FULL BOOT SEAL BLACK, 1/4-40 UNS 2-B THREADED NUT	B1440804	1825612-3
1	HALF BOOT SEAL BLACK, 1/4-40 UNS 2-B THREADED NUT	BT1440004	1825619-1
1	HALF BOOT SEAL BLACK, 15/32-32 UNS 2-B THREADED NUT	BT1532204	1825600-2
1	6A-125VAC; 3A-250VAC, 0.270" LONG ROUND TOGGLE 1/4-40 BUSHING, DPDT-ON/ON, B TERMINALS	MTM206N	4-1437559-9
1	6A-125VAC; 3A-250VAC, LOCKING TOGGLE 1/4-40 BUSHING, SPDT-ON/ON, WIRE LUG TERMINALS	MTL106D	3-1437559-4
1	6A-125VAC; 3A-250VAC, 0.452" LONG LARGE DIA. ROUND TOGGLE 15/32 BUSHING, DPDT-ON/ON, WIRE LUG TERMINALS	MTG206N	1-1437559-8
1	6A-125VAC; 3A-250VAC, 0.485" LONG FLAT TOGGLE 1/4-40 BUSHING, SPDT-ON/OFF/ON, WIRE LUG TERMINALS	MTF106E	8-1437558-4
1	6A-125VAC; 3A-250VAC, 0.410" LONG ROUND TOGGLE 1/4-40 BUSHING W/ "O" RING SEAL, SPDT-(ON)/OFF/(ON), WIRE LUG TERMINALS	MTE106G	7-1437558-1
1	6A-125VAC; 3A-250VAC, 0.600" LONG ROUND TOGGLE WITH PLASTIC TIP 1/4-40 BUSHING, 3PDT-ON/ON, WIRE LUG TERMINALS	MTB306D	6-1437558-6
1	6A-125VAC; 3A-250VAC, 0.410" LONG ROUND TOGGLE 1/4-40 BUSHING, 4PDT-ON/ON, WIRE LUG TERMINALS	MTA406P	4-1437558-5
1	6A-125VAC; 3A-250VAC, 0.410" LONG ROUND TOGGLE 1/4-40 BUSHING, DPDT-ON/(ON), B TERMINALS	MTA206R	2-1437558-8
1	6A-125VAC; 3A-250VAC, 0.410" LONG ROUND TOGGLE 1/4-40 BUSHING, SPDT-ON/ON, WIRE LUG TERMINALS	MTA106D	1-1437558-0

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KIRAN HOLAL 07NOV2011	 TE Connectivity	
DIMENSIONS: mm 		CHK OTT, PETER		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD OTT, PETER	NAME SINGLE, DOUBLE, 3 AND 4 POLE, DOUBLE THROW, PRINTED CIRCUIT BOARD AND WIRE LUG TERMINALS GREEN SERIES WITH BOOT SEALS KIT	
MATERIAL		PRODUCT SPEC	SIZE A3	
FINISH		APPLICATION SPEC	CAGE CODE	DRAWING NO
		WEIGHT	00779	1-2110843-1
		CUSTOMER DRAWING		RESTRICTED TO
		SCALE 1:1		SHEET 1 OF 1
				REV A