







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	RESIN SUPPLIER CHANGE FOR THE HOUSING	10MAY2022	SCB	PS



SECTION X—X




RECOMMENDED BOARD MOUNTING
(RECOMMENDED BOARD THICKNESS: .055—.103)



- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE OF BEAMS).
- 2 TOLERANCE NON-CUMULATIVE.
- 3 THE MATING END OF THE CONTACT IS IDENTIFIED BY THE LETTER "A" STAMPED ON THE RECEPTACLE BOX AS WELL AS THE WHITE STRIPE LOCATED ON THE TOP OF THE HOUSING.
- 4 MATERIAL: HOUSING — FLAME RETARDANT THERMOPLASTIC, COLOR— BLACK.
CONTACTS — PHOS BRONZE.
- 5 FINISH: CONTACTS— .000079 MIN THK TIN PLATE.

1.872	1.716	12	1-147534-2
B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN	03NOV00	 TE Connectivity	
DIMENSIONS: INCHES		CHK M ZITTO	02NOV00		
		APVD M ZITTO	02NOV00	NAME ASSY, MOD I, BOARD MOUNT RECP, .156 CL, HIGH PRESSURE, TYPE C, FOR ROUND HOLE MOUNTING	
		PRODUCT SPEC 108-25,016	APPLICATION SPEC 114-25,004		
MATERIAL SEE NOTE 4		FINISH SEE NOTE 5	WEIGHT —	SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C-147534	RESTRICTED TO —
				SCALE 4:1	SHEET 1 OF 1
				REV C	