



			1,800	900	40	9-1734516-0
OBsolete			1,800	900	38	8-1734516-8
OBsolete			1,800	900	36	8-1734516-6
OBsolete			1,800	900	34	8-1734516-4
OBsolete			1,800	900	32	8-1734516-2
			1,800	900	30	8-1734516-0
OBsolete			1,800	900	28	7-1734516-8
OBsolete			1,800	900	26	7-1734516-6
OBsolete			2,700	900	24	7-1734516-4
OBsolete			2,700	900	22	7-1734516-2
OBsolete			2,700	900	20	7-1734516-0
OBsolete			2,700	900	18	6-1734516-8
OBsolete			2,700	900	16	6-1734516-6
OBsolete			2,700	900	14	6-1734516-4
OBsolete			2,700	900	12	6-1734516-2
			2,700	900	10	6-1734516-0
			2,700	900	8	5-1734516-8
			1,800	900	40	4-1734516-0
OBsolete			1,800	900	38	3-1734516-8
OBsolete			1,800	900	36	3-1734516-6
OBsolete			1,800	900	34	3-1734516-4
OBsolete			1,800	900	32	3-1734516-2
OBsolete			1,800	900	30	3-1734516-0
OBsolete			1,800	900	28	2-1734516-8
			1,800	900	26	2-1734516-6
OBsolete			2,700	900	24	2-1734516-4
OBsolete			2,700	900	22	2-1734516-2
			2,700	900	20	2-1734516-0
OBsolete			2,700	900	18	1-1734516-8
OBsolete			2,700	900	16	1-1734516-6
			2,700	900	14	1-1734516-4
OBsolete			2,700	900	12	1-1734516-2
OBsolete			2,700	900	10	1-1734516-0
OBsolete			2,700	900	8	0-1734516-8
	DIM B	DIM A (REEL WIDTH)	PCS/CARTON	PCS/REEL	No. of Contacts	PART NO.

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± 1
1 PLC	± 0
2 PLC	± 0
3 PLC	± 0
4 PLC	± 1

[illegible]

SEE SHEET 1

SEE SHEET 1



TE Connectivity

S	NAME
---	------

AMPMODU 2.0mm PITCH, REC
CONN, SMT, VERTICAL MOUNT

SIZE

CAGE CODE

E	DRAWING NO
---	------------

RESTRICTED TO

A3	00779
----	-------

9 | C-1734516

SCALE 5:1

SHEET 2 OF 2

REV	A4
-----	----