


REVISIONS

3D VIEW
SCALE 2/1



GENERAL TOLERANCES	
10 MAX	± 0.2
10 OVER 30 MAX	± 0.25
30 OVER	± 0.3
ANGLES	$\pm 3^\circ$



 TRADE MARK, CAVITY MARK


 0.5 MAX. WARPAGE ARE PERMISSIBLE





(A1)	2	GRAY	PA66	CLIP HSG	1743455-3
	1	BLACK	B PA66	CLIP HSG	1743455-2
	NO.	COLOR	MATERIAL	DESCRIPTION	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JM JEON	11JUL2023		TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED		NAME	CLIP HSG FOR 090 MLC (TYPE3)	
		APVD JW JUNG	PRODUCT SPEC	-		
0 PLC ±.1 1 PLC ±0.1 2 PLC ±0.01 3 PLC ±0.001 4 PLC ±0.0001 ANGLES ±.1		APPLICATION SPEC	-	SIZE	CAGE CODE	DRAWING NO
MATERIAL TBD		FINISH	WEIGHT	A2	00779	G=1743455
CUSTOMER DRAWING;RESTRICTED CUSTOMER				SCALE	4:1	SHEET 1 OF 3
				REV	B	


#1-1743455-2
CONVERSION PART.
MISSING DIMENSIONS ARE SAME WIHT 1743455-2



1-1743455-X
3D VIEW



SECTION A-A
SCALE 4:1





A2	3	BLACK	PA66	B	CLIP HSG	I-1743455-2
NO.	COLOR	MATERIAL	DESCRIPTION	P/N		


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN -	11 JUL 2023			
DIMENSIONS: mm		CHK -	SEE SHEET 1 OF 2			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME CLIP HSG FOR 090 MLC (TYPE3)			
0 PLC ±		PRODUCT SPEC -	SIZE A2			
1 PLC ±0.1		APPLICATION SPEC -	CAGE CODE 00779			
2 PLC ±0.01		WEIGHT -	DRAWING NO C-1743455			
3 PLC ±0.001		CUSTOMER DRAWING; RESTRICTED CUSTOMER	RESTRICTED TO			
4 PLC ±0.0001		SCALE 4:1	SHEET 2 OF 3			
ANGLES ±			REV B			
FINISH -						
MATERIAL TBD						

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1	SEE SHEET 1		

#2-1743455-2
CONVERSION PART.
MISSING DIMENSIONS ARE SAME WIHT 1743455-2







2-1743455-X
3D VIEW




PANNEL HOLE SIZE

PANNEL THICKNESS : 0.5 ~ 2.7mm



SECTION A-A



A3	4	BLACK	PA66(B)	CLIP HSG	2-1743455-2
	NO.	COLOR	MATERIAL	DESCRIPTION	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN -	TE Connectivity					
		CHK -						
		APVD -						
		PRODUCT SPEC -						
DIMENSIONS: mm		SEE SHEET 1		NAME CLIP HSG FOR 090 MLC (TYPE3)				
				-				
				APPLICATION SPEC -				
				SIZE A2				
				CAGE CODE 00779				
MATERIAL SEE TABLE		FINISH -		DRAWING NO C-1743455		RESTRICTED TO		
				CUSTOMER DRAWING		SCALE 4:1	SHEET 3 OF 3	REV B