


1

10

1

A



VIEW D-D
NOT TO SCALE

Left Side
Connector(s): LC-Duplex Secure
Mode: MM
Housing Color: Violet
Geom. Spec: N/A

Fiber Path

A - _____ - Fiber B
B - _____ - Fiber A

Notes:

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Includes dust caps (not shown on print).
- 3 IL tested at 1300nm.
- 4 Label 2 will not be present on any cable assembly less than 5 meters long.

	A	Rev Per EC# RELEASE	1/25/2008	-	.
P	LTR	REVISION RECORD	DATE	DIN	A

DIMENSIONS: meters		YOUR/ANGES UNLESS OTHERWISE SPECIFIED:		CHK Joe Davis		
		0 P/LC * *		APVD Joe Davis	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608	
		1 P/LC * *		NAME	FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex Secure to MT-RJ (No Pins)	
		2 P/LC * *				
		3 P/LC * *				
		4 P/LC * *				
Restricted To:		SCALE NTS	SIZE A2	DRAWING NO C- 1907140	SHEET 1 of 4	REV A

Restricted To:

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.
PAGE NO

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Part #	L (meters)	L (feet)	LC-Duplex Secure, Violet		MT-RJ (No Pins), Black	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-1907140-1	0.950 - 1.050	3.11 - 3.44	0.5	-	0.5	20
0-1907140-2	1.950 - 2.050	6.39 - 6.72	0.5	-	0.5	20
0-1907140-3	2.950 - 3.050	9.67 - 10.00	0.5	-	0.5	20
0-1907140-4	3.920 - 4.080	12.86 - 13.38	0.51	-	0.51	20
0-1907140-5	4.920 - 5.080	16.14 - 16.66	0.51	-	0.51	20
0-1907140-6	5.920 - 6.080	19.42 - 19.94	0.51	-	0.51	20
0-1907140-7	6.920 - 7.080	22.70 - 23.22	0.51	-	0.51	20
0-1907140-8	7.920 - 8.080	25.98 - 26.50	0.51	-	0.51	20
0-1907140-9	8.850 - 9.150	29.03 - 30.01	0.51	-	0.51	20
1-1907140-0	9.850 - 10.150	32.31 - 33.30	0.52	-	0.52	20
1-1907140-1	10.850 - 11.150	35.59 - 36.58	0.52	-	0.52	20
1-1907140-2	11.850 - 12.150	38.87 - 39.86	0.52	-	0.52	20
1-1907140-3	12.850 - 13.150	42.15 - 43.14	0.52	-	0.52	20
1-1907140-4	13.850 - 14.150	45.43 - 46.42	0.52	-	0.52	20
1-1907140-5	14.850 - 15.150	48.72 - 49.70	0.52	-	0.52	20
1-1907140-6	15.840 - 16.160	51.96 - 53.01	0.52	-	0.52	20
1-1907140-7	16.830 - 17.170	55.21 - 56.33	0.53	-	0.53	20
1-1907140-8	17.820 - 18.180	58.46 - 59.64	0.53	-	0.53	20
1-1907140-9	18.810 - 19.190	61.71 - 62.95	0.53	-	0.53	20
2-1907140-0	19.800 - 20.200	64.96 - 66.27	0.53	-	0.53	20
2-1907140-1	20.790 - 21.210	68.20 - 69.58	0.53	-	0.53	20
2-1907140-2	21.780 - 22.220	71.45 - 72.90	0.53	-	0.53	20
2-1907140-3	22.770 - 23.230	74.70 - 76.21	0.53	-	0.53	20
2-1907140-4	23.760 - 24.240	77.95 - 79.52	0.54	-	0.54	20
2-1907140-5	24.750 - 25.250	81.20 - 82.84	0.54	-	0.54	20
2-1907140-6	25.740 - 26.260	84.44 - 86.15	0.54	-	0.54	20
2-1907140-7	26.730 - 27.270	87.69 - 89.46	0.54	-	0.54	20
2-1907140-8	27.720 - 28.280	90.94 - 92.78	0.54	-	0.54	20
2-1907140-9	28.710 - 29.290	94.19 - 96.09	0.54	-	0.54	20
3-1907140-0	29.700 - 30.300	97.44 - 99.40	0.55	-	0.55	20
3-1907140-1	30.690 - 31.310	100.68 - 102.72	0.55	-	0.55	20
3-1907140-2	31.680 - 32.320	103.93 - 106.03	0.55	-	0.55	20
3-1907140-3	32.670 - 33.330	107.18 - 109.35	0.55	-	0.55	20
3-1907140-4	33.660 - 34.340	110.43 - 112.66	0.55	-	0.55	20
3-1907140-5	34.650 - 35.350	113.68 - 115.97	0.55	-	0.55	20
3-1907140-6	35.640 - 36.360	116.92 - 119.29	0.55	-	0.55	20
3-1907140-7	36.630 - 37.370	120.17 - 122.60	0.56	-	0.56	20
3-1907140-8	37.620 - 38.380	123.42 - 125.91	0.56	-	0.56	20
3-1907140-9	38.610 - 39.390	126.67 - 129.23	0.56	-	0.56	20
4-1907140-0	39.600 - 40.400	129.92 - 132.54	0.56	-	0.56	20
4-1907140-1	40.590 - 41.410	133.16 - 135.85	0.56	-	0.56	20
4-1907140-2	41.580 - 42.420	136.41 - 139.17	0.56	-	0.56	20

Qty	U of M	Description	Item No.
2	piece	Trace Label	14
2	piece	Eyelet/Shrink tube assembly - White	13
1	piece	MT-RJ TwinZip Bend Limiting Boot, Beige	12
AR	meter	2 fiber, XG-50/125, 1.8mm, Twinzip, Aqua, OFNR (Riser)	11
1	piece	MT-RJ FERRULE, THERMOPLAST,MM	10
2	piece	LC Connector Assy, 1.6mm-2.0mm, MM	9
1	piece	LC Duplex clip, black	8
2	piece	LC, SC, FC Straight Boot, Beige	7
1	piece	CRIMP EYELET, MT-RJ	6
1	piece	MT-RJ, SPRING PUSH, UNIVERSAL	5
1	piece	PIN KEEPER, 3.8MM	4
1	piece	SPRING, MT-RJ, 3.8 DESIGN	3
1	piece	DUST COVER, MT-RJ	2
1	piece	HOUSING, CONN, MT-RJ,BLACK	1

DIMENSIONS: meters	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	9 P.L.C. ± . 1 P.L.C. ± . 2 P.L.C. ± . 3 P.L.C. ± . 4 P.L.C. ± .

Restricted To:

DWG Cable Assy Configurator		MATERIAL -	HEAT TREAT -	
CHK Joe Davis	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD Joe Davis				
NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex Secure to MT-RJ (No Pins)				
SCALE NTS	SIZE A2	DRAWING NO C- 1907140	SHEET 2 of 4	REV A

8 7 6 5 4 3 2 1

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

8

7

6

5

4

3

2

1

Part #	L (meters)	L (feet)	LC-Duplex Secure, Violet		MT-RJ (No Pins), Black	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
4-1907140-3	42.570 - 43.430	139.66 - 142.48	0.56	-	0.56	20
4-1907140-4	43.560 - 44.440	142.91 - 145.80	0.57	-	0.57	20
4-1907140-5	44.550 - 45.450	146.16 - 149.11	0.57	-	0.57	20
4-1907140-6	45.540 - 46.460	149.40 - 152.42	0.57	-	0.57	20
4-1907140-7	46.530 - 47.470	152.65 - 155.74	0.57	-	0.57	20
4-1907140-8	47.520 - 48.480	155.90 - 159.05	0.57	-	0.57	20
4-1907140-9	48.510 - 49.490	159.15 - 162.36	0.57	-	0.57	20
5-1907140-0	49.500 - 50.500	162.40 - 165.68	0.58	-	0.58	20
5-1907140-1	50.490 - 51.510	165.64 - 168.99	0.58	-	0.58	20
5-1907140-2	51.480 - 52.520	168.89 - 172.30	0.58	-	0.58	20
5-1907140-3	52.470 - 53.530	172.14 - 175.62	0.58	-	0.58	20
5-1907140-4	53.460 - 54.540	175.39 - 178.93	0.58	-	0.58	20
5-1907140-5	54.450 - 55.550	178.64 - 182.25	0.58	-	0.58	20
5-1907140-6	55.440 - 56.560	181.88 - 185.56	0.58	-	0.58	20
5-1907140-7	56.430 - 57.570	185.13 - 188.87	0.59	-	0.59	20
5-1907140-8	57.420 - 58.580	188.38 - 192.19	0.59	-	0.59	20
5-1907140-9	58.410 - 59.590	191.63 - 195.50	0.59	-	0.59	20
6-1907140-0	59.400 - 60.600	194.88 - 198.81	0.59	-	0.59	20
6-1907140-1	60.390 - 61.610	198.12 - 202.13	0.59	-	0.59	20
6-1907140-2	61.380 - 62.620	201.37 - 205.44	0.59	-	0.59	20
6-1907140-3	62.370 - 63.630	204.62 - 208.75	0.59	-	0.59	20
6-1907140-4	63.360 - 64.640	207.87 - 212.07	0.6	-	0.6	20
6-1907140-5	64.350 - 65.650	211.12 - 215.38	0.6	-	0.6	20
6-1907140-6	65.340 - 66.660	214.37 - 218.70	0.6	-	0.6	20
6-1907140-7	66.330 - 67.670	217.61 - 222.01	0.6	-	0.6	20
6-1907140-8	67.320 - 68.680	220.86 - 225.32	0.6	-	0.6	20
6-1907140-9	68.310 - 69.690	224.11 - 228.64	0.6	-	0.6	20
7-1907140-0	69.300 - 70.700	227.36 - 231.95	0.61	-	0.61	20
7-1907140-1	70.290 - 71.710	230.61 - 235.26	0.61	-	0.61	20
7-1907140-2	71.280 - 72.720	233.85 - 238.58	0.61	-	0.61	20
7-1907140-3	72.270 - 73.730	237.10 - 241.89	0.61	-	0.61	20
7-1907140-4	73.260 - 74.740	240.35 - 245.20	0.61	-	0.61	20
7-1907140-5	74.250 - 75.750	243.60 - 248.52	0.61	-	0.61	20
7-1907140-6	75.240 - 76.760	246.85 - 251.83	0.61	-	0.61	20
7-1907140-7	76.230 - 77.770	250.09 - 255.15	0.62	-	0.62	20
7-1907140-8	77.220 - 78.780	253.34 - 258.46	0.62	-	0.62	20
7-1907140-9	78.210 - 79.790	256.59 - 261.77	0.62	-	0.62	20
8-1907140-0	79.200 - 80.800	259.84 - 265.09	0.62	-	0.62	20

	A	Rev Per EC#	RELEASE	1/25/2008	-	JF			
P	LTR		REVISION RECORD	DATE	DIN	AP			

DIMENSIONS;
meters



TOLERANCES UNLESS OTHERWISE SPECIFIED		
0 PLC	$\pm$	"
1 PLC	$\pm$	"
2 PLC	$\pm$	"
3 PLC	$\pm$	"
4 PLC	$\pm$	"

Restricted To:

Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK	Joe Davis	 Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD	Joe Davis			
NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex Secure to MT-RJ (No Pins)				
SCALE NTS	SIZE A2	DRAWING NO C- 1907140	SHEET 3 of 4	REV A

D

C

B

A

CO AFFILIATES, IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

8

7

6

5

4

3

2

1

Label 1

Per specification 107-1645-1



—Trace # - Bar Code

[illegible]

-Trace # - Human Readable

Logo

Made in XXXX

X-XXXXXXXX-X

-Part Number

–Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



—Trace # - Bar Code

XXXXXXXXXXXXXXXXXXXX

—Trace # - Human Readable

Logo

Made in XXXX

X-XXXXXXX-X

—Part Number

—Country of Origin

This label is used on all lengths on this drawing.

USED ON

D

C

B

A

	A	Rev Per EC#	RELEASE	1/25/2008	-	JG				
P	LTR	REVISION RECORD			DATE	DIN	AP			

DIMENSIONS;
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED		
0 PLC	$\pm$	-
1 PLC	$\pm$	-
2 PLC	$\pm$	-
3 PLC	$\pm$	-
4 PLC	$\pm$	-

Restricted To:

DWN Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
CHK Joe Davis					
APVD Joe Davis					
NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex Secure to MT-RJ (No Pins)					
SCALE NTS	SIZE A2	DRAWING NO C- 1907140	SHEET 4 of 4	REV A	