







- (1) MATERIAL: HOUSING-NYLON, UL94V-0
(COLOR-NATURAL, COLOR OF PARTS MAY VARY)
CONTACTS-0.25 [.010] THICK BRASS ALLOY.
- (2) TYCO ELECTRONICS LOGO AND MATERIAL ID MAY BE LOCATED ON EITHER LONG SIDE OF PART.
- (3) CONTACT FINISH: 0.002032 [.000080] MIN BRIGHT TIN OVER 0.000762 [.000030] MIN NICKEL OVER ENTIRE CONTACT.
- 4 MATES WITH VAL-U-LOK(TM) RECEPTACLE HOUSINGS.
- (5) "O" WITH POST
"x" WITHOUT POST
- (6) PRELIMINARY-NOT FOR PRODUCTION
- (7) ADD LUBE



RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.78 MAX THICK P.C. BOARD
COMPONENT SIDE SHOWN

						18	12.6	4	2-2029056-4
	○	×	×	○		18	12.6	4	 1-2029056-4
						22.2	16.8	5	2029056-5
						18	12.6	4	2029056-4
						13.8	8.4	3	2029056-3
	1	2	3	4	5	DIM B	DIM A	NO. OF POSITIONS	PART NO
PIN POSITION 									
THIS DRAWING IS A CONTROLLED DOCUMENT.						DWN K. WHITAKER 11JAN2008	 TE Connectivity		
						CHK C. CASH 11JAN2008			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD C. CASH 11JAN2008	NAME		
		0. PLC	±	-		PRODUCT SPEC	PLUG ASSEMBLY, VERTICAL, SINGLE ROW, 94V-0, W/DRAIN HOLES, VAL-U-LOK(TM)		
		1. PLC	±	0.2		108-2112			
		2. PLC	±	0.13					
		3. PLC	±	-					
		4. PLC	±	-		APPLICATION SPEC	SIZE A100779C=2029056		
		ANGLES	±	-	0°30'	114-13172			
MATERIAL		FINISH				WEIGHT	RESTRICTED TO		
						-	-		
CUSTOMER DRAWING						SCALE N/A	SHEET 1 OF 1	REV B1	