


Thermofit[®] Molded Parts
 Specification Control Drawing
 Limited Distribution

Part Number : 202A111-25-01/225
 Description : Boot, Straight, Overexpanded

NOTES

- All dimensions are in $\frac{\text{inches}}{[\text{millimeters}]}$
- Dimensions appearing in table are as follows:
 - a - As Supplied
 - b - After Unrestricted Recovery
- Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.



PART NUMBER	H		J		P ±10% b	R ±10% b	JO Ref b	W ±20% b
	Min a	Max b	Min a	Max b				
	202A111-25-01/225	.75 [19,0]	.31 [7,9]	.75 [19,0]				

Raychem

RAYCHEM CORPORATION
 300 CONSTITUTION DRIVE
 MENLO PARK, CALIFORNIA 94025


Revision : A
 Date : 4/21/99

Part Number : 202A111-25-01/225
 Description : Boot, Straight, Overexpanded

Thermofit[®] Molded Parts
 Specification Control Drawing
 Limited Distribution

Part Number : 202A111-25-01/225
 Description : Boot, Straight, Overexpanded

MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-25	Elastomer, Fluid Resistant	RT-1325	/225	S-1206	Adhesive



THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION

Raychem

RAYCHEM CORPORATION
 300 CONSTITUTION DRIVE
 MENLO PARK, CALIFORNIA 94025

Revision : A
 Date : 4/21/99

Part Number : 202A111-25-01/225
 Description : Boot, Straight, Overexpanded