


LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
J	—	A	RELEASED	06AUG14	DM	TK



- ① オイル塗布タイプ
② 推奨工程：自動機械
③ 推奨工程：手動
④ 材料；NBRフタル酸フリー

- ① OIL COATED TYPE
② RECOMMENDED PROCESS: AUTOMATIC MACHINE
③ RECOMMENDED PROCESS: MANUAL
④ MATERIAL;NBR NON-BIS TYPE

WIRE RANGE
0.2~0.5 (AV, AVS)
mm² (AWG#24-#20)

INSULATION DIA.
 $\phi 1.4 \sim \phi 2.4$ mm

②

NBR ④

BLACK

2822352-2

③

NBR ①④

BLACK

2822352-1

MATERIAL

COLOR

PART NUMBER

DIMENSIONS:

mm

DWN 06AUG2014

D.MATSUURA

CHK 06AUG2014

S.IWATANI

APVD 06AUG2014

T.KOHNO

PRODUCT SPEC

108-5262

APPLICATION SPEC

—

WEIGHT

0.1 g

MATERIAL


SEE TABLE

FINISH

—

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± —



NAME

070 TYPE RUBBER PLUG

SIZE

A4

CAGE CODE

00779

DRAWING NO

C-2822352

RESTRICTED TO

—

CUSTOMER DRAWING

SCALE 10:1

SHEET

1 OF 1

REV A

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT - By Tyco Electronics Japan G.K.