

SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN mm)

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)

SILICON RUBBER
GASKET

J. POWER TIMER CNT. with SEAL

SUPPLIED WITH
"SLIDE" ON
CLOSED POSITION.

CLOSED CAVITY

ALTERNATIVE TE LOGO ADMITTED

RESTRICTED

THE DESIGN CONFIGURATION OF THIS PRODUCT IS
RESTRICTED BEFORE USE CONTACT THE CHIEF
ENGINEER OF AMP ITALIA. THE TECHNOLOGY IS
FREE FOR AMP USE.

UNPUBLISHED COPY

THIS INFORMATION IS CONFIDENTIAL AND IS
DISCLOSED TO YOU ON CONDITION THAT NO
FURTHER DISCLOSURE IS MADE BY YOU TO OTHER
THAN AMP PERSONNEL WITHOUT A WRITTEN
AUTHORIZATION FROM AMP ITALIA SPA.

2x	2x	2	SEC. LOCK RED	PA 6.6 10-15% G.F.	282315-1	
1x	=	1	HOUSING ASS'Y GREY	PA 6.6 10-15% G.F.	282313-3	
=	1x	1	HOUSING ASS'Y BLACK	PA 6.6 10-15% G.F.	282313-1	
282311-3	282311-1	POS.	FINITURA COLORE (FINISH) COLOUR)	MATERIALE (MATERIAL)	NUMERO (PART NUMBER)	
		ASS'Y P/N	CUSTOMER DWG. FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO	
			THIS DRAWING IS UNPUBLISHED			
© COPYRIGHT 1989 BY AMP INC. RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING						

A2	ALTERNATIVE TE LOGO ADDED	A.B.	06/09/2014	± 0.3
A1	MODIFIED per ET0440-96	D.B.	01/09/2014	± 2°
A	RELEASED per ET0091-96	D.B.	15 FEB. 1993	
3	REVISED	E.CINI	15 FEB. 1993	
2	REVISED	E.C.	15 FEB. 1993	
1	REDRAWN WAS 91-51018	E.C.	15 FEB. 1993	
REV.	REVISIONT (REVISION RECORD)	DIS.	DATA (DATE)	
		APP.	(APP.)	
				I A3 C-282311
				A2 1