





LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	OWN
			J	REVISED PER ECR-13-004343	30JUL13	KH
						APVD
						KR

- 1 FITS 0.81±0.025 X 4.75 [.032±.001 X .187] TAB
- 2 WIRE SIZE: 0.3–0.9mm² [22–18 AWG], STRANDED ONLY.
STRIP LENGTH 7.14 [.281]
- 3 INSULATION SIZE: 4.19 [.165] MAX DIA.
- 4 SUPPLIED AS LOOSE PIECE



OBSOLETE	TYPE 6/6 NYLON	RED TRANSLUCENT	0.41 [.016] #4H PH BRZ	TIN	2-520337-4
	TYPE 6/6 NYLON	RED TRANSLUCENT	BRASS	TIN	2-520337-2
	MATERIAL	COLOR	MATERIAL	FINISH	PART NO
	HOUSING			TERMINAL	
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN P FORTNEY 8/10/90	TE Connectivity RECEPTACLE ASSEMBLY,ULTRA-FAST FLAG, 4.75 [.187] SERIES,LOOSE PIECE	
DIMENSIONS: mm[INCHES] 		CHK MS FEHER 8/23/90			
		APVD D BRATINA 8/24/90			
		PRODUCT SPEC 108-2043			
MATERIAL SEE TABLE		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.38 [.015] 3 PLC ± - 4 PLC ± - ANGLES ± -	NAME	SIZE A2	
		APPLICATION SPEC 114-2123	CAGE CODE 00779		
		WEIGHT -	DRAWING NO C-520337		
CUSTOMER DRAWING			SCALE 8:1	SHEET 1 of 1	REV J