

SPECIFICATION CONTROL DRAWING


55PC1826TITLE
TWO CONDUCTOR CABLE, SHIELDED, JACKETED, 600 VOLTDate
6-28-95

Revision

This specification sheet forms a part of the latest issue of Raychem Specification 55PC.

COMPONENT WIRES - 55PC0816

SHIELD - NICKEL-COATED COPPER

JACKET - RADIATION-CROSSLINKED,
MODIFIED ETFE

CONSTRUCTION DETAILS

PART NUMBER	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (in.)		DIAMETER (in.)			WEIGHT (lbs/1000 ft.)	
			LOWER SPEC LIMIT	TARGET WALL	LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT
55PC1826-24-*	24	38	.0055	.0070	.114	.118	.122	10.32	10.77
55PC1826-22-*	22	38	.0055	.0070	.126	.130	.134	12.93	13.42
55PC1826-20-*	20	38	.0055	.0070	.143	.147	.151	17.00	17.56
55PC1826-18-*	18	38	.0060	.0075	.163	.168	.173	22.96	23.73
55PC1826-16-*	16	38	.0060	.0075	.179	.184	.189	27.68	28.48

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms)**CROSSLINK VERIFICATION: 300 ± 3°C for 1 hour****DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz****JACKET COLOR: White preferred****JACKET ELONGATION AND TENSILE STRENGTH:**

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)**JACKET FLAWS:**

Spark Test, 1000 volts (rms), 60 Hz, 100% test

Impulse Dielectric Test, 6.0 kV (peak), 100 % test

SHIELD COVERAGE: 85% (minimum)**VOLTAGE WITHSTAND TEST (POST ENVIRONMENTAL):**

1000 volts (rms), 60 Hz, 1 minute

PART NUMBER:

The "*" in the part numbers above shall be replaced by a color code designator with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

Example: AWG 22, red and blue component wires;
white jacket: 55PC1826-22-2/6-9

COLOR AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HERIN. REFERENCED
DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF CITATION FOR BID.

Raychem

Raychem Corporation
300 Constitution Drive, Menlo Park, CA 94025
1-800-2-Raychem Fax 1-415-361-6297