

SPECIFICATION CONTROL DRAWING

55PC4221

TITLE

TWO CONDUCTOR CABLE, JACKETED, 600 VOLT

Date

3-27-96

Revision

D

This specification sheet forms a part of the latest issue of Raychem Specification 55PC.

COMPONENT WIRES - 55PC0211

JACKET - RADIATION-CROSSLINKED,
MODIFIED ETFE



CONSTRUCTION DETAILS

PART NUMBER	CONDUCTOR SIZE (AWG)	JACKET THICKNESS (in.)		DIAMETER (in.)			WEIGHT (lbs/1000 ft.)	
		LOWER SPEC LIMIT	TARGET WALL	LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT
55PC4221-24-*	24	.0050	.0065	.088	.092	.096	5.35	5.76
55PC4221-22-*	22	.0050	.0065	.100	.104	.108	7.36	7.81
55PC4221-20-*	20	.0055	.0070	.117	.122	.127	10.69	11.23
55PC4221-18-*	18	.0055	.0070	.136	.141	.146	15.42	16.15
55PC4221-16-*	16	.0055	.0070	.151	.156	.161	19.22	19.98
55PC4221-14-*	14	.0060	.0075	.182	.187	.192	28.96	29.96
55PC4221-12-*	12	.0060	.0080	.220	.226	.232	43.59	44.89

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms)

DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

CROSSLINK VERIFICATION: 300 ± 3°C for 1 hour

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)

PART NUMBER:

The "" in the part numbers above shall be replaced by a color code designator with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

Example: AWG 20, red and blue component wires;
white jacket: 55PC4221-20-2/6-9

COLOR AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681.

Raychem

Raychem Corporation
300 Constitution Drive, Menlo Park, California 94025
1-800-2 Raychem FAX: 415-361