



1	BLACK #30 AWG	P
2	WHITE #30 AWG	
3	RED #30 AWG	P
4	GREEN #30 AWG	
5	BROWN #30 AWG	P
6	BLUE #30 AWG	
7	ORANGE #30 AWG	P
8	YELLOW #30 AWG	
9	VIOLET #30 AWG	P
10	GRAY #30 AWG	
11	TAN #30 AWG	P
12	PINK #30 AWG	
13	WHITE/BLUE #30 AWG	P
14	BLUE/WHITE #30 AWG	
15	GREEN/YELLOW #30 AWG	
	SHIELD	DRAIN
	SHIELD	DRAIN

- ① CABLE; 7.5 PAIR, 30 AWG (7/38) TIN PLATED COPPER WITH PVC INSULATION. 2 DRAIN WIRES AND A ALUMINUM/POLYESTER SHIELD.
- ASSEMBLY INSPECTED FOR OPENS AND SHORTS.
  - CABLE ASSEMBLY ALL BLACK IN COLOR, WITH NO PRINT ON JACKET.
  - MATERIALS ARE UL RECOGNIZED.

	12.00±.50	621612-3
	72.00±1.00	621612-2
OBSOLETE	12.00±.50	621612-1
	L	PART NO

WIRE RANGE		DIMENSIONS: INCHES		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
-		DIMENSIONS APPLY BEFORE PLATING		NAME	
-		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CABLE ASSY, PIGTAIL, INFOPORT SERIES III, 15 POSN, KEY 2	
INSUL RANGE	2 PLC ± - 3 PLC ± - ANGLES ± -	CHK	10-6-95	SCALE	REV
WV	-	J.HAMMER	-	2:1	A2
REELING	107--	APVD	-	DRAWING NO	621612
SPLICE	115--	T.SMITH	-	SHEET	1 OF 1
					H

				APPL FEED	TRIMMING BURR
				-	-
				WDW	IDW
				-	-
H	PER ECR-08-002168	30JAN08	JAK CR	REELING	107--
P	LTR	REVISION RECORD	DATE DWN APVD	SPLICE	115--

WIRING DIAGRAM

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA, USA.

LOC  
CF  
DIST  
39