



MOD	LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	87146
30	AD	39				B	REDRAWN	11-6-89	-
						C	REV LOC & DIST AD-4171	3-90	BF
						D	OBS PER 0010-0743-93	9/14/93	PS
						E	OBS PER 0010-0774-93	12-7-93	PS
						F	OBS PER 0010-1031-93	12-7-93	PS
						G	OBS PER 0010-1049-93	12-7-93	PS
						H	REV PER 0010-1043-93	3-11-94	PS
						J	REV PER 0010-0768-93	3-11-94	PS
						K	REV PER 0010-0728-94	5-31-94	PS
						L	OBS -7 PER 0010-0665-96	30DEC96	JH
						M	REV PER 0G3C-0093-00	28MAR00	DS
						N	REV PER 0G3C-0203-04	13OCT04	JR/DS



1 CAVITY LOCATION DIMENSIONS INCREASE IN INCREMENTS OF .150±.003 TOLERANCE NON-COMULATIVE

2. USE EXTRACTION TOOL #91052-1 TO REMOVE RECEPTACLES FROM HOUSING.

3. THIS HOUSING HAS NO MARKING WHATSOEVER.

OBSOLETE	3.590	1.650	1.800	48	1-87146-7
OBSOLETE	4.490	2.100	2.250	60	1-87146-6
OBSOLETE	3.140	1.500	1.500	42	1-87146-5
	2.990	1.350	1.500	40	1-87146-4
OBSOLETE	2.390	1.050	1.200	32	1-87146-3
OBSOLETE	2.240	1.050	1.050	30	1-87146-2
OBSOLETE	2.090	.900	1.050	28	1-87146-1
OBSOLETE	1.640	.750	.750	22	1-87146-0
OBSOLETE	1.490	.600	.750	20	87146-9
OBSOLETE	1.340	.600	.600	18	87146-8
OBSOLETE	1.190	.450	.600	16	87146-7
OBSOLETE	1.040	.450	.450	14	87146-6
OBSOLETE	.890	.300	.450	12	87146-5
OBSOLETE	.740	.300	.300	10	87146-4
OBSOLETE	.590	.150	.300	8	87146-3
OBSOLETE	.440	.150	.150	6	87146-2
OBSOLETE	.290	-	.150	4	87146-1
	C	B	A	NO. OF POS.	PART NUMBER

				PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± .005 ANGLES ± -	DR 11-6-89 BOB BOLES	AMP AMP INCORPORATED Harrisburg, Pa. 17105			
	CHK 11-21-89 J. GESFORD				
	APPD 11-21-89 J. GESFORD	NAME			
MATERIAL GLASS FILLED NYLON, COLOR-BLACK PER ASTM D4066	APPD 11-21-89 R. ELICKER	HOUSING, MOD IV, .150 X .150 GRID, DOUBLE ROW, CRIMP SNAP-IN.			
	PRODUCT SPEC -				
FINISH -	APPLICATION SPEC -	SIZE C	FSCM NO 00779	DRAWING NO 87146	
	WEIGHT -	SCALE 4:1		SHEET 1 OF 1	