

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	Initial Release	19DEC2019	RS	DV

Slit Adhesive Sleeve
(S-1048)




Table: Dimensions (inches)

Size	Extruded ID (A)	Cut Length (B)	Extruded Wall (C)
SAS-090-1.00-1048	.090 ± .005	1.000 ± .050	.024± .005
SAS-115-1.00-1048	.115 ± .005	1.000 ± .050	.032± .005
SAS-160-1.00-1048	.160 ± .005	1.000 ± .050	.032± .005
SAS-200-1.00-1048	.200 ± .005	1.000 ± .050	.035± .005
SAS-250-1.00-1048	.250 ± .010	1.000 ± .050	.035± .005
SAS-300-1.00-1048	.300 ± .010	1.000 ± .050	.067± .010

Color: Amber


Requirement: The Silt Adhesive Sleeves shall meet all the requirements of TE specification 108-20052.

RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

© COPYRIGHT - TE Connectivity Ltd.

DIMENSIONS:		DWN	15MAY2019	MATERIAL		FINISH	
INCHES		RS		-			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	19DEC2019	 TE Connectivity			
		HL					
		APVD	19DEC2019				
		DV					
		PRODUCT SPEC					
0 PLC	± -	-		NAME			
1 PLC	± -						
2 PLC	± -			SLIT ADHESIVE SLEEVE SAS-XXX-XXX-1048			
3 PLC	± -						
4 PLC	± -						
ANGLES	± -	APPLICATION SPEC		RESTRICTED TO			
		108-120052		SIZE	CAGE CODE	DRAWING NO	
		WEIGHT		A4	06090	C-	SAS-XXX-XXX-1048
		-					
CUSTOMER DRAWING						SCALE	1:1
						SHEET	1 OF 1
						REV	A