



Raychem S200 Shield Terminators

Fast, Easy Shield Termination and Grounding to 200°C

Raychem S200 Shield Terminators

High-Performance, High-Temperature Cable Terminators



Heat-Shrinkable Sleeve for Fast, Reliable, Economical Cable Shield Termination and Grounding

An important extension of the Raychem SolderSleeve family, S200 shield termination devices were developed specifically to address the need for high-temperature connecting, insulating, and sealing for applications in the aerospace and defense industry.





ECONOMICAL

- One-piece design allows for a single-step, simplified installation and a low total installed cost
- Bi-alloy or thermochromic temperature indicator works as a process control aid and simplifies operator training
- Offered in various sizes and ground lead configurations

CAPABLE

- Provides a completely soldered, strain-relieved termination
- Heat-shrinkable sleeve helps provide insulation, inspectability, and strain relief
- Designed for high-temperature applications up to 200°C
- Sealing inserts helps ensure reliable, environmental protection

APPLICATIONS

- Shield termination of cables subjected to a minimum temperature rating of 150°C and maximum operating temperature of 200°C
- Protecting and sealing for BMS 13-60 PTFE wrapped cables and M27500 cables with PTFE/polyimide jackets

Wide Selection

Offered in various sizes and ground lead configurations, our S200 shield termination devices provide environmentally protected shield termination on cables with a minimum temperature rating of 150°C, and silver or nickel-plated shields. They are also available with bi-alloy or thermochromic indicators

Fast Installation and Lower Costs

Convenient to use, the one-piece design of S200 shield termination devices help ensure reliable environmental protection and greatly simplified installation for a lower total installed cost.

MATERIALS

- **Solder:** Tin 96%/Silver 4% bi-alloy solder
- **Tubing:** Heat-shrinkable modified fluoropolymer
- **Inserts:** Thermoplastic fluoropolymer

STANDARDS AND SPECIFICATIONS

- **Industry Standards:**
SAE-AMS-DTL-23053/13 (applies to heat-shrinkable insulation sleeve only)
SAE-AS83519 (modified for 200°C applications)
EU RoHS/ELV compliant
- **TE Instruction Sheet:** RCPS-100-71
- **TE Qualification and Test Report:** Available on request

MECHANICAL/ENVIRONMENTAL

- **Operating Temperature:** 150°C to 200°C
- **Durability:** Heat-shrinkable sleeve adheres and seals to provide a completely soldered, strain-relieved termination

TE Components . . . TE Technology . . . TE Know-how . . .

AMP | AGASTAT | CII | HARTMAN | KILOVAC | MICRODOT | NANONICS | POLAMCO | Raychem | Rochester | DEUTSCH
SEACON Phoenix | LL ROWE | Phoenix Optix | AFP | SEACON

Empower Engineers to Solve Problems, Moving the World Forward.


ORDERING INFORMATION (TC indicates that this part has a thermochromic indicator)

Without ground lead

Jacket OD (mm)	Shield (mm)	Product Description	Raychem Part Number	SAE AS83519
1.90	0.90	S200-1-00	F92583-000	
1.90	0.90	S200-1-00-TC	CN5417-000	
2.67	1.40	S200-2-00	F94898-000	
2.67	1.40	S200-2-00-TC	CN5418-000	
4.32	2.15	S200-3-00	A65903-000	
4.32	2.15	S200-3-00-TC	CN5419-000	
5.97	3.30	S200-4-00	E32454-000	
5.97	3.30	S200-4-00-TC	CN5420-000	
6.98	4.30	S200-5-00	D12074-000	
6.98	4.30	S200-5-00-TC	CN5421-000	

With pre-installed braid: Nickel-plated copper strands in accordance to AA59569F36N0031. (6 Inches)

Jacket OD (mm)	Shield (mm)	Product Description	Raychem Part Number	SAE AS83519
1.90	0.90	S200-1-01	CS5526-000	M83519/5-1
2.67	1.40	S200-2-01	D08259-000	M83519/5-2
4.32	2.15	S200-3-01	A77145-000	M83519/5-3
5.97	3.30	S200-4-01	F26506-000	M83519/5-4
6.98	4.30	S200-5-01	A18826-000	M83519/5-5

With pre-installed braid: Ni-plated copper strands per ASTM B355, Class 4. CMA = 1200. (6 Inches)

Jacket OD (mm)	Shield (mm)	Product Description	Raychem Part Number	SAE AS83519
1.90	0.90	S200-1-9020	CJ1037-000	M83519/5-11
1.90	0.90	S200-1-9020-TC	CP7589-000	M83519/5-16
2.67	1.40	S200-2-9020	CJ1039-000	M83519/5-12
2.67	1.40	S200-2-9020-TC	CP4262-000	M83519/5-17
4.32	2.15	S200-3-9020	CJ1041-000	M83519/5-13
4.32	2.15	S200-3-9020-TC	CP6063-000	M83519/5-18
5.97	3.30	S200-4-9020	CJ1042-000	M83519/5-14
5.97	3.30	S200-4-9020-TC	CP6893-000	M83519/5-19
6.98	4.30	S200-5-9020	CJ1043-000	M83519/5-15
6.98	4.30	S200-5-9020-TC	CP7313-000	M83519/5-20

With pre-installed braid: Ni-plated copper strands per ASTM B355, Class 4. CMA = 1800. (6 Inches)

Jacket OD (mm)	Shield (mm)	Product Description	Raychem Part Number	SAE AS83519
1.90	0.90	S200-1-9030	CA7639-000	
2.67	1.40	S200-2-9030	CA7640-000	
4.32	2.15	S200-3-9030	CA7641-000	
5.97	3.30	S200-4-9030	CA7642-000	
6.98	4.30	S200-5-9030	CA7643-000	
6.98	4.30	S200-5-9030-TC	CP7417-000	



With pre-installed braid: High nickel-plated copper strands per ASTM-B355 Class 7. CMA = 640. (10 Inches)

Jacket OD (mm)	Shield (mm)	Product Description	Raychem Part Number	SAE AS83519
1.90	0.90	S200-1-01-100HN	D89883-000	
2.67	1.40	S200-2-01-100HN	A87947-000	
4.30	2.15	S200-3-01-100HN	A59779-000	
5.95	3.30	S200-4-01-100HN	C69495-000	
6.90	4.30	S200-5-01-100HN	D92195-000	

With pre-installed braid: Stranded nickel-plated copper wire in accordance with SAE-AS22759/41.

Jacket OD (mm)	Shield (mm)	Product Description	Raychem Part Number	SAE AS83519
1.90	0.90	S200-1-55-22-9	EH1934-000	
2.67	1.40	S200-2-55-22-9	EH1935-000	
4.30	2.15	S200-3-55-22-9	EH1936-000	
5.95	3.30	S200-4-55-22-9	EH1938-000	
6.90	4.30	S200-5-55-22-9	EH1939-000	

With pre-installed braid: Stranded nickel-plated copper wire in accordance with SAE-AS22759/41.

Jacket OD (mm)	Shield (mm)	Product Description	Raychem Part Number	SAE AS83519
1.90	0.90	S200-1-55-20-9	EH1940-000	
2.67	1.40	S200-2-55-20-9	EH1941-000	
4.30	2.15	S200-3-55-20-9	EH1942-000	
5.95	3.30	S200-4-55-20-9	EH1943-000	
6.90	4.30	S200-5-55-20-9	EH1944-000	

With pre-installed braid: Stranded nickel-plated copper wire in accordance with SAE-AS22759/41.

Jacket OD (mm)	Shield (mm)	Product Description	Raychem Part Number	SAE AS83519
1.90	0.90	S200-1-55-18-9	EH1945-000	
2.67	1.40	S200-2-55-18-9	EH1946-000	
4.30	2.15	S200-3-55-18-9	EH1948-000	
5.95	3.30	S200-4-55-18-9	EH1949-000	
6.90	4.30	S200-5-55-18-9	EH1950-000	

LET'S CONNECT

We make it easy to connect with our experts and are ready to provide all the support you need. Just call your local support number or visit te.com to chat with a Product Information Specialist.

Technical Support

te.com/support-center

North America	+1 800 522 6752	Asia Pacific	+86 400 820 6015
North America (Toll)	+1 717 986 7777	Japan	+81 044 844 8180
EMEA/South Africa	+800 0440 5100	Australia	+61 2 9554 2695
EMEA (Toll)	+31 73 624 6999	New Zealand	+64 (0) 9 634 4580
India (Toll-Free)	+800 440 5100		

te.com/ADM

AMP, AGASTAT, CII, DEUTSCH, HARTMAN, KILOVAC, LL ROWE, MICRODOT, NANONICS, POLAMCO, Raychem, SEACON, SolderSleeve, TE, TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Corporation. Other products, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information herein, nothing herein constitutes any guarantee that such information is error-free, or any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. The TE entity issuing this publication reserves the right to make any adjustments to the information contained herein at any time without notice. All implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose are expressly disclaimed. The dimensions herein are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice.

Consult TE for the latest dimensions and design specifications.

© 2017 TE Connectivity Corporation All Rights Reserved.

1-1773851-1 07/17