





COIL: @ +25 °C
 RESISTANCE 440 OHMS ± 10%
 NOMINAL VOLTAGE 15.0-23 VDC
 MUST OPERATE 9.9 VDC
 MUST RELEASE 6.0 VDC MAX 1.1 VDC MIN

ENVIRONMENT:
 VIBRATION 10 CPS TO 2000 CPS @ 20 g's
 SHOCK 100 g's 11 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 4 MS MAX
 CONTACT BOUNCE 2 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2A
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 5/22/92 CK. 5/26/92 gmb

**COMMUNICATIONS
 INSTRUMENTS, INC.**

CUST. GENICOM
 CUST. NO. 3SAV5004F1

TYPE "HFW" RELAY

HFW1201S171