






LOC	DIST	REVISIONS				
CE	17	P	LTR	DESCRIPTION	DATE	OWN
			A	RELEASED	16MAR07	DLF



DETAIL C
TYP. 6 PLC.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. FENNELL	16MAR07	tyco Electronics		Tyco Electronics Corporation Harrisburg, PA 17105-3608		
		CHK D. FENNELL	16MAR07					
		APVD D. FENNELL	16MAR07	NAME				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CASSETTE, 6 PORT, SINGLEMODE, MPO TO LC, STRAIGHT FIBER PATH				
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC — APPLICATION SPEC —				
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO
—		—		A2	00779	C=1938060		—
CUSTOMER DRAWING					SCALE	SHEET		REV
					NTS	1 of 2		A

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

CE

17

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

1. MAXIMUM CASSETTE ASSEMBLY LOSS: 1.25dB.

2

WHITE MARKING ON MPO TO BE FACING TOWARD TOP OF CONNECTOR MODULE. WHITE MARK INDICATES FIBER 1 SIDE.

3

SEE TRACE LABEL DETAIL.

4. A COPY OF CASSETTE ASSEMBLY LOSS TEST DATA WILL BE PLACED INSIDE OR WITH THE UNIT PACKAGE. CASSETTES WILL BE TESTED AT 1310nm AND 1550nm WAVELENGTHS.

5. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230–702.

3

tycoXXXXXXXXXXXXXX

SINGLEMODESTRAIGHT1938060–X

MADE IN USA

FIBER PATH – STRAIGHT

MPO L1 PORT POSITION NO	LC PORT POSITION NO
1	1B
2	1A
3	2B
4	2A
5	3B
6	3A
7	4B
8	4A
9	5B
10	5A
11	6B
12	6A

AQUA SECURE	AQUA SECURE	1–1938060–1
SLATE SECURE	SLATE SECURE	1–1938060–0
ROSE SECURE	ROSE SECURE	1938060–9
VIOLET SECURE	VIOLET SECURE	1938060–8
BROWN SECURE	BROWN SECURE	1938060–7
ORANGE SECURE	ORANGE SECURE	1938060–6
YELLOW SECURE	YELLOW SECURE	1938060–5
BLUE SECURE	BLUE SECURE	1938060–4
GREEN SECURE	GREEN SECURE	1938060–3
RED SECURE	RED SECURE	1938060–2
BLACK STANDARD	BLUE STANDARD	1938060–1
MPO COUPLING BUSHING COLOR & TYPE	LC ADAPTER COLOR & TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± –

1 PLC ± –

2 PLC ± –

3 PLC ± –

4 PLC ± –

ANGLES ± –

FINISH

—

DWN
D. FENNELL
08NOV06

CHK
D. FENNELL
08NOV06

APVD
D. FENNELL
08NOV06

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

—

CUSTOMER DRAWING

tyco

Electronics

Tyco Electronics Corporation
Harrisburg, PA 17105–3608

NAME
CASSETTE, 6 PORT, SINGLEMODE,
MPO TO LC, STRAIGHT FIBER PATH

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1938060

RESTRICTED TO

—

SCALE
NTS

SHEET
2 of 2

REV
A

1938060

AMP 3307–7 REV 31MAR2000