


A	1		2				3				4	
	Old P/N	Tyco Electronics P/N	Maß a ²⁾	Maß b ¹⁾	Maß c ²⁾	Maß d ¹⁾	Maß e ¹⁾	Maß f ¹⁾	Maß g ⁴⁾	Maß h ⁴⁾	Maß i ⁴⁾	SW des 6-Kt. -Profils
	-P23	6-1393670-5	2.1	3	3.5	4.5	9.2	26	3	5	11	3.8 ±0.02
	-P23A	6-1393670-6	2.1	3	3.5	4.5	9.2	26	3	5	11	3.8 ±0.02
	-P25	6-1393670-7	3.8	5.55	6.5	7.85	12.2	29	3	5	12.5	6.8 ±0.02

Active Part numbers. Contact Tyco Electronics for other configuration availability



Maße des Steckgesichts nach DIN 47297 und CECC 22230

Kontaktteile: Kupfer-Beryllium

Kontaktfläche: vergoldet

Isolierteile: PTFE


Innenleiter mit Crimpanschluß:

□ 0.7 für ST 212

□ 1 für ST 214

Montage vorschritt: MV 2: Datenbuch Seite 4.49

Kabelaufbauformung:



4) Nennmaß

3) Beschriftet mit Siemens

2) Kleinstmaß

1) Größtmaß

tyco

Tyco Electronics Corporation

Oostkamp - Belgium



LOC
GW

DIMENSIONS
IN MM

SCALE 5:1

WEIGHT

MATERIAL

PART NAME

Cable Plug 1.0/2.3
with Quick Lock Coupling

PART NO.

V23614-A109-P***-*-27

SHT.

OF

DATE	03.10.91
NAME	Mattheeuws
DEP.	PD Com
EC	
TOLERANCE UNLESS SPECIFIED OTHERWISE	
REV.	CHANGE ORDER
DATE	APP.
Customer Drawing No : C 6-1393670-5	

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA USA.

PROPRIETARY: