



DESIGNED FOR USE WITH RG-58/U, 141, & 303 CABLES	
CABLE ENTRY DIAMETER MINIMUM	
CONTACT	.042
SLEEVE	.122
FERRULE	.205

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
02 ₁	REVISED	2/11/97	[Signature]
B	PER EC 0U20-0692-00	9/25/01	C. Huang 9/25/01

HOUSING CLAMP NUT COUPLING NUT	BRASS PER ASTM-B-16, HALF HARD	NICKEL PLATE PER QQ-N-290
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BRASS PER ASTM-B-16, HALF HARD	GOLD PLATE PER MIL-G-45204
INNER SLEEVE	BRASS PER ASTM-B-16, HALF HARD	GOLD PLATE PER MIL-G-45204
RETAINING RING	PHOSPHOR BRONZE PER QQ-B-750, GRADE B2	N/A
GASKET	SILICONE RUBBER PER ZZ-R-765	N/A
SHRINK TUBING	HEAT SHRINKABLE POLYOLEFIN COMPOUND MIL-I-23053/4	N/A
FERRULE	COPPER OR BRASS ALLOY ROCKWELL F65 MAXIMUM	GOLD PLATE PER MIL-G-45204

COMPONENT	MATERIAL	FINISH
-----------	----------	--------

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	DRAWN BY TJG	DATE 10/29/79	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599
	CHECKED BY RRS	3/4/80	
	APPD BY GH	3/7/80	

These drawings and specifications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASSY PROCEDURE	TITLE "OSN" STRAIGHT CABLE PLUG-CRIMP ATTACHMENT		
	NO. AP. 408-04889 (30-050)	SIZE B	CODE IDENT NO. 26805	3031-7358-10
		SCALE 3:1		REV 02 ₁

NOTES:
1. CAPTURED CENTER CONTACT

.XXX = in
XX.X = mm (REF)

CUSTOMER DRAWING

AMP PART # 1057245-1
SHEET 1 OF 1 REV B