

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	ECR-11-011294	26MAY2011	SR	AR
	B2	ECR-11-011684	06JUN2011	SR	AR
	B3	ECR-11-012551	16JUN2011	VG	AR
	B4	ADDED RETENTION FORCE	26JUN2023	G.K	S.P

- 1

2.5 µm Sn OVER 1.3 µm Ni
- 31

2

PACKAGING:
30 PIN HEADER PACKED IN TRAY
8 TRAYS PACKED INTO SHIPPING BOX
TOTAL PACKAGING UNIT PER BOX: 240 PARTS
- 3

ALL

6.5

 DIMENSIONS

0.1

 C-D
- 4

WAVE SOLDER CAPABLE TO 240° C
- 5

PIN RETENTION FORCE IN X-DIRECTION MIN. 20N
- 1

2.5 µm Sn UEBER 1.3 µm Ni
- 31

2

VERPACKUNG:
30 STIFTSTECKER IN PRODUKTTRAEGER VERPACKT
8 PRODUKTTRAEGER VERPACKT IN KARTON
KOMPLETTPACK EINHEIT: 240 TEILE
- 3

ALLE

6.5




 MASSE

0.1



 C-D
- 4

LOETFAEHIGKEIT BIS MAX. 240° C
- 5


PIN-HALTEKRAFT IN X-RICHTUNG MIN. 20N



RECOMMENDED PC-BOARD LAYOUT
EMPFOHLENES LEITERPLATTENLAYOUT



INSTALLATION HEIGHT OF PIN HEADER FOR SAFE CONTACTING WITH SOCKET CONNECTOR
EINBAUHÖHE DER STIFTLISTE FUER SICHERE KONTAKTIERUNG MIT BUCHSENSTECKER



-	-	-	35	-	PIN STIFT	2
-	-	-	1	1	PIN HOUSING STIFTGEHAEUSE	1
-	-	-	-1	REV.	DESCRIPTION	ITEM NO
-	-	-	-	←	REVISION OF EACH ASSY NO. (WHEN BLANK, USE DWG. REVISION)	
QTY REQD PER ASSY			PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 290CT2010 R.SCHNEIDER CHK 290CT2010 A.ROESGEN APVD 290CT2010 Z.LAMPERT PRODUCT SPEC 108-1329 APPLICATION SPEC 114-16016 WEIGHT - CUSTOMER DRAWING			NAME AMP SEAL PIN HEADER 35 POS. - SIZE A2 CAGE CODE 00779 DRAWING NO C=1103599 RESTRICTED TO -		
SCALE 5:1			SHEET 1 OF 1			REV B4		