




NOTES


- SUITABLE CABLE GLANDS:
CUSTOMER DRAWING: 1102770
- STANDARDS:
DIN EN 61984; DIN EN 60664-1
- PACKAGING:
3 SETS IN A CARTON,
ALL COMPONENTS NOT PRE-
MOUNTED AND PACKED LOOSE



CABLE GLAND LOCKED BY
SCREW INSTANT ADHESIVE



PN 0-1
AS SHOWN



OBSOLETE

QTY	DESCRIPTION	MATERIAL	SURFACE	COLOR	NOTE / ORDERING TEXT	ITEM	
2	ASS'Y CRIMP BARREL	COPPER	SILVER PLATED	--	WIRE SIZE 120MM ²	9	
- 2	ASS'Y CRIMP BARREL	COPPER	SILVER PLATED	---	WIRE SIZE 95 MM ²	8	
1	CODING SET HF13	--	--	--	--	7	
- 1	CODING SET HF8	--	--	--	--	6	
2	SCREW INSTANT ADHESIVE	--	--	--	--	5	
2	ASS'Y CABLE GLAND	BRASS	NICKEL PLATED	--	M32	4	
2	ASS'Y FEMALE INSERT	PA6.6-GF25	-	BLACK	HF.13/16.Bu	3	
1	ASS'Y FIXING PLATE	STEEL	ZINC PLATED	--	HF.8.2XHF.13.ST	2	
1	ASS'Y HOOD	--	CROMIT AL TCP PASS.	BLACK	HF-EMVK.8.STO.2.M32.G+1.M8	1	
0-2	0-1	DESCRIPTION	MATERIAL	SURFACE	COLOR	NOTE / ORDERING TEXT	ITEM
	X	HF.8.STO.2M32.G+1.M8.95					
X		HF.8.STO.2M32.G+1.M8.120					

THIS DRAWING IS A CONTROLLED DOCUMENT. DATE: 16.08.2008
 DISE ZERZEHNUNG IST EIN KONTROLLIERTES DOKUMENT. CHK: J.BRAUN

TE Connectivity
 SET HOOD
 SERIES HF8

SCALE: 1:2
 SHEET: 1 OF 1
 REV: C1