


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
C2		CONTACT PIN PN CHANGED	06JUL2021	SB	KJK

POS	L±0.4	PART NUMBER
2	5.08	1241013-2
3	7.62	
4	10.16	1241013-4
5	12.70	
6	15.24	
7	17.78	
8	20.32	
9	22.86	
10	25.40	1-1241013-0
11	27.94	
12	30.48	
13	33.02	1-1241013-3
14	35.56	
15	38.10	1-1241013-5
16	40.64	
17	43.18	
18	45.72	
19	48.26	
20	50.80	
21	53.34	
22	55.88	
23	58.42	
24	60.96	
25	63.50	
26	66.04	
27	68.58	
28	71.12	
29	73.66	
30	76.20	
31	78.74	
32	81.28	
33	83.82	
34	86.36	
35	88.90	
36	91.44	
37	93.98	
38	96.52	
39	99.06	
40	101.60	
41	104.14	
42	106.68	
43	109.22	
44	111.76	
45	114.30	
46	116.84	
47	119.38	
48	121.92	
49	124.46	
50	127.00	



NOTES:

1. PIN HEADER PACKED IN FOLDING BOX

- 2 n. ISO 8015
n. ISO 2768 - mH -E
n. DIN 16901 - 140

3 BARE EDGES PERMITTED IN THIS AREA

© 2021 TE Connectivity. All Rights Reserved.

ITEM NO.	DESCRIPTION	MATERIAL	SURFACE / COLOR
2	CONTACT PIN	CuSn	PRE-TIN PLATED
1	PIN HOUSING	PBT-GV	GREEN

MATERIAL	FINISH
-	-

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±0.2
1 PLC	±0.2
2 PLC	±0.1
3 PLC	±
4 PLC	±
ANGLES	±

DWN M. STEIN	20JAN1998
CHK F. REICHARDT	20JAN1998
APVD G. FELDMEIER	20JAN1998
PRODUCT SPEC	108-18012
APPLICATION SPEC	-
WEIGHT	-

TE TE Connectivity

NAME AMPMODU II PIN HEADER, SINGLE ROW			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A 4	00779	C=1241013	-

CUSTOMER DRAWING	SCALE	SHEET	REV
	4:1	1 OF 1	C2