

MATED WITH: PASSEND ZU:		LOC AI	DIST —	REVISIONS AENDERUNGEN DESCRIPTION BESCHREIBUNG					DATE	DWN	APVD
—				P	LTR						
PROJEKT NR.: —					A2	SEE EG00-2458-99			16DEC99	VB	—
SEE TABLE DRAWING 1241638											
—		—	—	—	—	—	—	—	—	—	
CUSTOMER PART NO		AMP PART NO		REV.	PCS.	MATERIAL		SURFACE COLOR	DESCRIPTION		
DIMENSIONS: DIMENSIONEN: mm		DWN v/d Burgt		12 NOV 99		MATERIAL —		FINISH OBERFLAECHE/FARBE —			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN n. ISO 8015 n. ISO 2768 - mH -E n. DIN 16901 - 140 p. PLC ±- p. PLC ±- p. PLC ±- p. PLC ±- ANGLES/WINKEL ±-		CHK D. Kuempel		12 NOV 99		AMP AMP Deutschland GmbH D - 63225 Langen					
		APVD —		—							
		PRODUCT SPEC PRODUKTSPEZ. 108-18476-1		APPLICATION SPEC VERARBEITUNGSSPEZ. 114-18141-1		NAME POWER QUADLOK, SOCKET CONTACT Power Quadlok, Buchsenkontakt		RESTRICTED TO NUR FUER —			
				WEIGHT GEWICHT —		SIZE A4		CAGE CODE 00779		DRAWING NO ZEICHNUNGS-NR. C-1241602	
CUSTOMER DRAWING		/KUNDENZEICHNUNG				MASSSTAB —		BLATT 1 OF VON 1		A2	