






REVISONS		DATE	DWN	APVD
B1	CHANGE IN TOLERANCE FOR DIMENSIUON 10.75	17DEC2014	NV	PS



**Schnittstelle 114-18284**  
**Interface 114-18284**



**NOTES**  
 Bemerkungen

- 1 AMP-LOGO  
AMP-Logo
- 2 ORDER-NUMBER  
Bestell-Nummer
- 3 REVISIONS-NUMBER  
Werkzeugeaenderungsindex
- 4 -
- 5 CAVITY MARKING  
Nestmarkierung
- 6 -
- 7 PACKAGING IN CARTON  
Verpackung in Karton
- 8 MATERIAL MARKING  
Werkstoffkennzeichnung
- 9 DASH NUMBER DEPENDS ON FINISHING MACHINE  
Strichzahl ist abhaengig von der Verarbeitungsmaschine

-I AS SHOWN  
 -I wie gezeichnet

Part No.	Rev.	QTY	Material	Finish	Notes
929318-1	929308-1	0.35-0.5mm <sup>2</sup>	CuSn4	vorverzinkt	-
963720-1	965969-1	0.35-0.5mm <sup>2</sup>	CuSn4	vorverzinkt	878635-734723-1
167418-1	167419-1	0.2-0.56mm <sup>2</sup>	CuSn	vorverzinkt	872006-654188-2
AMP-Bestell-Nummer		DGB (FLR)	Werkstoff	Oberflaeche	Crimp-Werkzeuge
Bandware Einzelausf.					Masch.-Werkz. Handzange
Kontakte					

PART NO.	REV.	PCS.	MATERIAL	SURFACE COLOR	DESCRIPTION	ITEM NO.
1241680-1	B	1	PA66	BLACK	4POS. MODU IV HSG.	-

DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.15 1 PLC ±0.15 2 PLC ±0.15 3 PLC ±0.15 4 PLC ±0.15 ANGLES ±°	
MATERIAL: PA66 FINISH: -		WEIGHT: - CUSTOMER DRAWING: -	

DWN: M. Reinhardt CHK: H. Schmitt APVD: -	DATE: 14APR99 NAME: 4POS. MODU IV SOCKETHOUSING 4pol. MODU IV Buchsengehäuse
SIZE: A CAGE CODE: 00779 DRAWING NO: 1241680	RESTRICTED TO: - SCALE: 1:1 SHEET: 1 OF 1 REV: B1