




REVISIONS				
P	LTN	DESCRIPTION	DATE	APVD
E	3	REVISED PER ECO-16-002589	26FEB2016	NK JO
F		REVISED PER ECO-18-012301	06AUG2018	RS JO



- △ HOUSING: HIGH TEMPERATURE, GLASS FILLED NYLON, COLOR: BLACK.
CONTACTS: PHOSPHOR BRONZE.
- △ CONTACTS: 0.000381 MIN GOLD ON MATING RECEPTACLE END, 0.00254 BRIGHT TIN-LEAD ON REMAINDER, ALL OVER 0.001270 NICKEL.
- △ NO CONTACT IN THIS POSITION FOR PART NUMBER 1375965-2 & -5 ONLY.
- △ NO CONTACT IN THIS POSITION FOR PART NUMBER 1375965-3 & -6 ONLY.
- △ CONTACTS: 0.000381 MIN GOLD ON MATING RECEPTACLE END, 0.00254-0.00508 MATTE TIN ON REMAINDER, ALL OVER 0.001270 NICKEL.
- △ ROHS 2002/95/EC COMPLIANT PART TO BE USED WITH ROHS 2002/95/EC COMPLIANT PCB'S.



△ 6	△ 5	YES △ 4	1375967-6
△ 6	△ 5	YES △ 3	1375967-5
△ 6	△ 5	NO	1375967-4
	△ 2	YES △ 4	1375967-3
	△ 2	YES △ 3	1375967-2
	△ 2	NO	1375967-1
		FINISH	KEYED CIRCUITS
			PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT. DWN: W.G. LENKER 20JUN2000
 CHK: L. BREKOSKY 15JAN2001

STE TE Connectivity




NAME: ASSEMBLY, PC/104-PLUS, NON-STACKTHROUGH CONTACTS, SOLDER

PRODUCT SPEC: 108-1956
 APPLICATION SPEC: 114-13021

SIZE: A1 CAGE CODE: 100779 DRAWING NO: 1375967
 RESTRICTED TO: CUSTOMER DRAWING

SCALE: 5:1 SHEET 1 OF 2 REV F

REVISIONS				
P.	LTN	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W.G. LENKER 20JUN2000	
DIMENSIONS: mm		CHK L. BREKOSKY 15JAN2001	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME ASSEMBLY, PC/104-PLUS, NON-STACKTHROUGH CONTACTS, SOLDER
MATERIAL		APVD	PRODUCT SPEC 108-1956
FINISH		APVD	APPLICATION SPEC 114-13021
WEIGHT		APVD	RESTRICTED TO
CUSTOMER DRAWING		SCALE 5:1	SHEET 2 OF 2
SCALE 5:1		REV F	