


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		D		EC 03GC-0338-04	20AUG04	BSV	MZ

PICOD131ALULS
 1571505-1 ²



SPECIFICATIONS:

MATERIALS:

MOVABLE CONTACT: GOLD OVER NICKEL OVER COPPER ALLOY
 CASE: BLACK MATTE FINISH, PPO
 ACTUATOR BUTTONS: PPO
 FIXED CONTACTS: GOLD OVER NICKEL ON COPPER.
 TERMINALS: GOLD OVER NICKEL ON COPPER.
 WINDOW: THERMOPLASTIC RESIN
 PCB: GLASS EPOXY, TYPE FR4
 CHARACTER COLOR: WHITE ON BLACK BACKGROUND
 CHARACTER HEIGHT: 10-/16-DIGIT .122/.094

ELECTRICAL:

CONTACT RATING: 0.4 VA @ 20 VDC OR PEAK AC.
 CONTACT RESISTANCE: 0.15 OHMS MAX. (INCLUDES INTERNAL CIRCUIT RESISTANCE).
 INSULATION RESISTANCE: 1000 MEGOHMS MINIMUM.
 DIELECTRIC STRENGTH: 500V AC, 1 MINUTE.
 LIFE: PICOD: 1,000,000 OPERATIONS.

MECHANICAL:

OPERATING FORCE: APPROX. 11 OZ. (3 N)


ENVIRONMENTAL:

OPERATING TEMPERATURE: -4°F TO +140°F (-20°C TO +60°C).


NOTES:

- PICO137ALULS REPLACES PICO-00111F.
- ² THE SWITCHING MODE IS SHORTING SO THAT EVEN DURING ACTUATION AT LEAST ONE OUTPUT IS CONNECTED TO INPUT C.


OBSOLETE




PICOD137ALULS
 1571506-1




PICOD301ALUS
 2-1437601-1



OBSOLETE



PICOD131/1ALULS
 1571905-1



POS	0	1	2	3	4	5	6	7	8	9
C	X	X	X	X	X	X	X	X	X	X
1		X		X		X		X		X
2			X	X			X	X		
4					X	X	X	X		
8									X	X

POS	0	1	2	3	4	5	6	7	8	9
C	X	X	X	X	X	X	X	X	X	X
1	X		X		X		X		X	
2	X	X			X	X			X	X
4	X	X	X	X					X	X
8	X	X	X	X	X	X	X	X		

POS	0	1	2	3	4	5	6	7	8	9	A	B	C	D	E	F
C	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
1		X		X		X		X		X		X		X		X
2			X	X			X	X			X	X			X	X
4					X	X	X	X					X	X	X	X
8									X	X	X	X	X	X	X	X

WAS 80559-SD

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BSV	20AUG04	Tyco Electronics Corporation Harrisburg, Pa 17105-3808	
DIMENSIONS: INCHES		CHK -	-		
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME M. ZITTO	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .010 4 PLC ± - ANGLES ± 1°		PRODUCT SPEC -	
MATERIAL -		FINISH -		APPLICATION SPEC -	
		WEIGHT -		SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO 1437601-5	
				RESTRICTED TO -	SCALE 2:1
				SHEET 1 OF 1	REV D