


REVISIONS				
ZONE	LTR	ECN	DESCRIPTION	DATE
	P	23983	REVISED, REDRAWN, 003-0332-0001 WAS 003-0351-0001. SEE ECN.	HSU 2/19/79
	R	25703	NOTE A DELETE OVER NICKEL STRIKE. A.M.	4/24/81
	S	39938	GASKET WAS: 000-0011-0001	2/11/02



- NOTES:
1. MAX. LEAK RATE: 10^{-6} CC/HE/SEC. AT 1 ATM. PRESSURE DIFFERENTIAL
 2. .190-32 UNF-2A THD
 3. SILVER PLATE .0002 MIN. PER QQ-S-365, TYPE II, GRADE A.
 4. THIS CONNECTOR MATES WITH ALL SCREW-ON SERIES (S-50) PLUGS AS LISTED IN THE MALCO CATALOG.

1	003-0268-0000	GASKET	SILICONE RUBBER	3
1	003-0332-0001	INSULATOR	TEFLON PER L-P-403	2
1	005-0066-0001	SOCKET	IRON NICKEL ALLOY PER MIL-I-23011	
1	005-2518-0004	GLASS BEAD	GLASS	
1	005-0065-0001	HOUSING	STEEL PER QQ-S-637	
1	005-0677-0001	RECEPTACLE SUBASSY		1
QTY	PT. NO.	DESCRIPTION	MAT'L & SPEC	ITEM NO.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± .XXX ± .010		CONTRACT NO.		MALCO A MICRODOT COMPANY, INC. 306 PASADENA AVE., SO. PASADENA, CALIF. 91030	PROD. CODE 964 CODE CDM
MATERIAL NOTED		APPROVALS	DATE		
FINISH 3		DRAWN HSU	2/15/79		
NEXT ASSY		CHECKED <i>[Signature]</i>	2/14/79		
USED ON		PR. ENG. RAH	2/16/79	RECEPTACLE, HERMETIC	
APPLICATION		APPROVED		SIZE B	CODE IDENT NO. 98278
DO NOT SCALE DRAWING		These drawings and specifications are the property of Microdot Inc., are issued in strict confidence and shall not be divulged, be reproduced or copied, or used as the basis for the manufacture or sale of any article without written permission of Microdot Inc.		DRAWING NO. 051-0049-0001	
		SCALE 10X		SHEET 1 OF 1	