


NUMBER C154562

3rd ANGLE (AMERICAN) PROJECTION

DIMENSIONS IN INCHES. DO NOT SCALE PRINT
DIMENSIONS THUS [] IN MM.



154562-5	BRASS	ELECTRO-TIN	LOOSE PIECE
154562-4	BRASS	NICKEL	
154562-3	BRASS	ELECTRO-TIN	
154562-2	BRASS	PRE-TIN	
154562-1	BRASS	NONE	
PART NO	MATERIAL	FINISH	REMARKS

OBsolete
RECOMMENDED CAVITY DETAIL
0.010 [0.25] x 45° CHAMFER.
x .200 [5.08] DEEP.

A1				REVISED PER ECR-19-018140				MK	TD	26DEC 2019	
A - SANCED				OM				177%			
A1				REVISION RECORD				DR	CHK	DATE	
A - DENNETT				DE				APP			
A1				A1				A1			

© AMP of GREAT BRITAIN LTD 1973				CUSTOMER COPY REFERENCE ONLY			
MATERIAL AND FINISH 0.010 [0.25] x 45° CHAMFER. x .200 [5.08] DEEP.				STE TE Connectivity			
SEE TABLE.				CLASS			
WIRE - RANGE - INSULATION				TYPE			
TOLERANCE EXCEPT AS NOTED ± 0.15 [3.81] ± 1°				SCALE 4:1			
LOC 5				NO A C154562			
NAME BOBBIN TAD				REV A1			

PRINT DIST.

CAF 204/78