


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION .19
 © COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

REVISIONS					
REV	DATE	DESCRIPTION	ECN	DWN	APVD
0	11OCT01	RELEASED	FJ00-2067-01	S.A	N.S



- 1. 端子送りピッチ: 8.8mm
- 2. 取扱説明書; 411-5912
- 1. CONTACT FEED PITCH: 8.8mm
- 2. INSTRUCTION SHEET No; 411-5912

TIN PLATING	1565403-1
FINISH	PART NO

WIRE RANGE 包合電線断面積	0.08~0.14mm ²	INSULATION DIA 被覆外径	Ø1.1~1.4mm
-----------------------	--------------------------	------------------------	------------

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN S. AMEMIYA	11OCT01
DIMENSIONS: 単位: 概 mm		CHK N. SAI	11OCT01
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差: ±0.3		APVD N. SAI	11OCT01
0-PLC ±0.1		PRODUCT SPEC 108-5660	
1-PLC ±0.1		APPLICATION SPEC 114-5276	
2-PLC ±0.15		WEIGHT 0.23 g	
3-PLC ±0.001		CUSTOMER DRAWING	
4-PLC ±0.001			
ANGLES 仕上 ±3°00'			
FINISH 仕上 SEE TABLE			
MATERIAL 材料 CU Alloy			

AMP Tyco Electronics AMP K.K. Kawasaki, Japan		
NAME 名称 025 IDC RECEPTACLE CONTACT (0.08Sq)		
SIZE A2	CAGE CODE 番号 00779	DRAWING NO 1565403
SCALE 10.1	SHEET 1	REV 0