


REVISIONS

P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	E	ECR-15-017693	22JAN2016	JB	ED
	F	ECR-21-004872	27/04/21	JB	GN



1574150-1
1574150-5
1574150-6
PART NUMBER

1574150-4
PART NUMBER

1574150-3
PART NUMBER

1574150-7
PART NUMBER

REFERENCE	PN	CAPACITES PRINCIPAL CAPACITIES MAIN	CAPACITES DERIVE CAPACITIES TAP	MASSE WEIGHT	COUPLE DE RUPTURE BREAKING SHEAR HEAD TORQUE
P3X95	1574150-1	25 to 95mm <sup>2</sup>	25 to 95mm <sup>2</sup>	164g	18Nm
P3X95 CEC ALLEMAGNE	1574150-4			168g	
P3X95-2CE	1574150-3			170g	
P3X95 EDP	1574150-5			168g	
P3X95 MP	1574150-6			164g	
P3X95 S	1574150-7			165g	

MARQUAGE: LOGO, REFERENCE, CAPACITES, LOT  
MARKING: LOGO, REFERENCE, CAPACITIES, DATE

TOLERANCES UNLESS OTHERWISE SPECIFIED  
TOLERANCES NON SPECIFIEES: -

DIMENSIONS: mm	DWN / DESSINE C. ANDRE	09 FEB05	MATERIAL MATIERE	-	FINISH FINITION	-
	CHK / VERIFIE E. DEREY	-				
TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERANCES NON SPECIFIEES (SUIVANT DE DECIMALES): 0 PLC / DEC: ±0 1 PLC / DEC: ±0.1 2 PLC / DEC: ±0.2 3 PLC / DEC: ±0.3 4 PLC / DEC: ±0.4 ANGLES ±						
PRODUCT SPEC SPEC. PRODUIT			SIZE FORMAT	A4	DRAWING NO No PLAN	RESTRICTED TO RESERVE A
APPLICATION SPEC SPEC. APPLICATION			WEIGHT MASSE APPROX.	-	C=1574150	
CUSTOMER DRAWING / PLAN CLIENT		UNIQUEMENT POUR REFERENCE	SCALE ECHELLE	1:2	SHEET FEUILLE	OF DE
						REV F

printed on 27 Apr 2021 10:51 (Paris, Madrid) from E0000162

RELEASED FOR PUBLICATION  
LIBRE A LA DIFFUSION

ALL RIGHTS RESERVED.  
TOUS DROITS RESERVES.

THIS DRAWING IS UNPUBLISHED.  
DIFFUSION RESTREINTE

BY -  
COPYRIGHT 20