

TE P/N	TE CD	Nanonics P/N	Part Description
1589068-1	1589068	CX015PC2RC012	Coax, 50 ohm, 1 position w/ 5 signals, plug, 30 AWG RG-178 coaxial cable, 30 AWG 7 strand, color coded PTFE wire, 12 inches
1589068-2	1589068	CX035PC2RC006N	Coax, 50 ohm, 3 position w/ 5 signals, plug, 30 AWG RG-178 coaxial cable, 30 AWG 7 strand, color coded PTFE wire, 6 inches, 1.0 captive jackscrews.
1589068-3	1589068	CX035PC2RC018N	Coax, 50 ohm, 3 position w/ 5 signals, plug, 30AWG RG-178 coaxial cable, 30 AWG 7 strand, color coded PTFE wire, 18 inches, 1.0 captive jackscrews.
1589068-4	1589068	CX045PC2RC006N	Coax, 50 ohm, 4 position w/ 5 signals, plug, 30AWG RG-178 coaxial cable, 30 AWG 7 strand, color coded PTFE wire, 6 inches, 1.0 captive jackscrews.
1589068-5	1589068	CX015PC2RC012N	Coax, 50 ohm, 1 position w/ 5 signals, plug, 30AWG RG-178 coaxial cable, 30 AWG 7 strand, color coded PTFE wire, 12 inches, 1.0 captive jackscrews.
1589068-6	1589068	CX055PC2RC006N	Coax, 50 ohm, 5 position w/ 5 signals, plug, 30 AWG RG-178 coaxial cable, 30 AWG 7 strand, color coded PTFE wire, 6 inches, 1.0 captive jackscrews.
1589068-7	1589068	CX095PC2RC006N	Coax, 50 ohm, 9 position w/ 5 signals, plug, 30 AWG RG-178 coaxial cable, 30 AWG 7 strand, color coded PTFE wire, 6 inches, 1.0 captive jackscrews.
1589068-8	1589068	CX095PC2RC036N	Coax, 50 ohm, 9 position w/ 5 signals, plug, 30 AWG RG-178 coaxial cable, 30 AWG 7 strand, color coded PTFE wire, 36 inches, 1.0 captive jackscrews.
1589068-9	1589068	CX045PC2RC036N	Coax, 50 ohm, 4 position w/ 5 signals, plug, 30 AWG RG-178 coaxial cable, 30 AWG 7 strand, color coded PTFE wire, 36 inches, 1.0 captive jackscrews.
1-1589068-0	1589068	CX045PC2RC036Q	Coax, 50 ohm, 4 position w/ 5 signals, plug, 30 AWG RG-178 coaxial cable, 30 AWG 7 strand, color coded PTFE wire, 36 inches, 1.2 captive jackscrews.
1-1589068-1	1589068	CX025PC2RC018N	Coax, 50 ohm, 2 position w/ 5 signals, plug, 30 AWG RG-178 coaxial cable, 30 AWG 7 strand, color coded PTFE wire, 18 inches, 1.0 captive jackscrews.
1-1589068-2	1589068	CX055PC2RCM02N	Coax, 50 ohm, 5 position w/ 5 signals, plug, 30 AWG RG-178 coaxial cable, 30 AWG 7 strand, color coded PTFE wire, 2 meters, 1.0 captive jackscrews.
1-1589068-3	1589068	CX035PC2RC024Q	Coax, 50 ohm, 3 position w/ 5 signals, plug, 30 AWG RG-178 coaxial cable, 30 AWG 7 strand, color coded PTFE wire, 24 inches, 1.2 captive jackscrews.
1-1589068-4	1589068	CX045PC2RC014N	Coax, 50 ohm, 4 position w/ 5 signals, plug, 30 AWG RG-178 coaxial cable, 30 AWG 7 strand, color coded PTFE wire, 14 inches, 1.0 captive jackscrews.
1-1589068-5	1589068	CX055PC2RCM01N	Coax, 50 ohm, 5 position w/ 5 signals, plug, 30 AWG RG-178 coaxial cable, 30 AWG 7 strand, color coded PTFE wire, 1 meter, 1.0 captive jackscrews.
1-1589068-6	1589068	CX065PC2RC012Q	Coax, 50 ohm, 6 position w/ 5 signals, plug, 30 AWG RG-178 coaxial cable, 30 AWG 7 strand, color coded PTFE wire, 12 inches, 1.2 captive jackscrews.