





3-1589456-9	1589455	SSM037PC2DC024N	Dualobe, 1 row, metal, 37 position, plug, 30 AWG 7 strand, color coded PTFE wire, 24 inches, 1.0 captive jackscrews.
4-1589456-0	1589455	SSM037PC2DCM01N	Dualobe, 1 row, metal, 37 position, plug, 30AWG 7 strand, color coded PTFE wire, 1 meter, 1.0 captive jackscrews.
4-1589456-1	1589455	SSM037PC2DC15Q	OBSOLETE
4-1589456-2	1589455	SSM037PC2DX012Q	Dualobe, 1 row, metal, 37 position, plug, 30 AWG 7 strand, white PTFE wire, 12 inches, 1.2 captive jackscrews.
4-1589456-3	1589455	SSM037PC2DX018N	Dualobe, 1 row, metal, 37 position, plug, 30 AWG 7 strand, white PTFE wire, 18 inches, 1.0 captive jackscrews.
4-1589456-4	1589455	SSM037PC2GX030N	Dualobe, 1 row, metal, 37 position, plug, 30 AWG 7 strand, FEP ribbon cable, 30 centimeters, 1.0 captive jackscrews.
4-1589456-5	1589455	SSM051PC2DC006	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, color coded PTFE wire, 6 inches.
4-1589456-6	1589455	SSM051PC2DC006N	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, color coded PTFE wire, 6 inches, 1.0 captive jackscrews.
4-1589456-7	1589455	SSM051PC2DC012N	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches, 1.0 captive jackscrews.
4-1589456-8	1589455	SSM051PC2DC018	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, color coded PTFE wire, 18 inches.
4-1589456-9	1589455	SSM051PC2DC024	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, color coded PTFE wire, 24 inches.
5-1589456-0	1589455	SSM051PC2DC024N	Dualobe, 1 row, metal, 51 position, plug, 30AWG 7 strand, color coded PTFE wire, 24 inches, 1.0 captive jackscrews.
5-1589456-1	1589455	SSM051PC2DC030N	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, color coded PTFE wire, 30 inches, 1.0 captive jackscrews.
5-1589456-2	1589455	SSM051PC2DCC06Q	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, color coded PTFE wire, 6 centimeters, 1.2 captive jackscrews.
5-1589456-3	1589455	SSM051PC2DM012Q	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 12 inches, 1.2 captive jackscrews.
5-1589456-4	1589455	SSM051PC2DM024N	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 24 inches, 1.0 captive jackscrews.
5-1589456-5	1589455	SSM051PC2DMC10N	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 10 centimeters, 1.0 captive jackscrews.
5-1589456-6	1589455	SSM051PC2DMC30N	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 30 centimeters, 1.0 captive jackscrews.
5-1589456-7	1589455	SSM051PC2DNC06Q	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 6 centimeters, 1.2 captive jackscrews.
5-1589456-8	1589455	SSM051PC2DNC15Q	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 15 centimeters, thread for 1.2 jackscrews.
5-1589456-9	1589455	SSM051PC2DX008	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, white PTFE wire, 8 inches.
6-1589456-0	1589455	SSM051PC2DXM05Q	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, white PTFE wire, 5 meters, 1.2 captive jackscrews.
6-1589456-1	1589455	SSM051PC2DY012N	Dualobe, 1 row, metal, 15 position, plug, 30 AWG 7 strand, white PTFE M16878/6 wire, 12 inches, 1.0 captive jackscrews.
6-1589456-2	1589455	SSM051PC2GX012N	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, FEP ribbon cable, 12 inches, 1.0 jackscrews.
6-1589456-3	1589455	SSM005PC2DC012Q	Dualobe, 1 row, metal, 5 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches, 1.2 captive jackscrews.
6-1589456-4	1589455	SSL005PC2DC012N	Dualobe, 1 row, LCP, 5 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches, 1.0 captive jackscrew.
6-1589456-5	1589455	SSM009PC2DM024N	Dualobe, 1 row, metal, 9 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 24 inches, thread for 1.0 jackscrews.
6-1589456-6	1589455	SSM015PC2DC012M	Dualobe, 1 row, metal, 15 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches, 1.0 non captive jackscrews.
6-1589456-7	1589455	SSM051PC2DM018N	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 18 inches, 1.0 captive jackscrews.
6-1589456-8	1589455	SSM037PC0DC036N	Dualobe, 1 row, metal, 37 position, plug, 28 AWG, solid, color coded PTFE wire, 36 inches, 1.0 captive jackscrews.
6-1589456-9	1589455	SSM025PC0DC036N	Dualobe, 1 row, metal, 25 position, plug, 28 AWG solid, color coded PTFE wire, 36 inches, 1.0 captive jackscrews.
7-1589456-0	1589455	SSM005PC0DC036N	Dualobe, 1 row, metal, 5 position, plug, 28 AWG solid, color coded PTFE wire, 36 inches, 1.0 captive jackscrews.
7-1589456-1	1589455	SSM005PC2DC012M	Dualobe, 1 row, metal, 5 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches, 1.0 non captive jackscrews.
7-1589456-2	1589455	SSL015PC2DC024M	Dualobe, 1 row, LCP, 15 position, plug, 30 AWG 7 strand, color coded PTFE wire, 24 inches, 1.0 non captive jackscrews.
7-1589456-3	1589455	SSL005PC0DX012M	Dualobe, 1 row, LCP, 5 position, plug, 28 AWG solid, white PTFE wire, 12 inches, 1.0 non captive jackscrews.
7-1589456-4	1589455	SSL009PC0DX012M	Dualobe, 1 row, LCP, 9 position, plug, 28 AWG solid, white PTFE wire, 12 inches, 1.0 non captive jackscrews.
7-1589456-5	1589455	SSL015PC0DX012M	Dualobe, 1 row, LCP, 15 position, plug, 28 AWG solid, white PTFE wire, 12 inches, 1.0 non captive jackscrews.
7-1589456-6	1589455	SSL051PC0DX012M	Dualobe, 1 row, LCP, 51 position, plug, 28 AWG solid, white PTFE wire, 12 inches, 1.0 non captive jackscrews.
7-1589456-7	1589455	SSM025PC4DX015N	Dualobe, 1 row, metal, 25 position, plug, 34 AWG 7 strand, white PTFE wire, 15 inches, 1.0 captive jackscrews.
7-1589456-8	1589455	SSL025PC2DC024N	Dualobe, 1 row, LCP, 25 position, plug, 30 AWG 7 strand, color coded PTFE wire, 24 inches, 1.0 captive jackscrews.
7-1589456-9	1589455	SSL009PC2DC024N	Dualobe, 1 row, LCP, 9 position, plug, 30 AWG 7 strand, color coded PTFE wire, 24 inches, 1.0 captive jackscrews.
8-1589456-0	1589455	SSL037PC2DC018N	Dualobe, 1 row, LCP, 37 position, plug, 30 AWG 7 strand, color coded PTFE wire, 18 inches, 1.0 captive jackscrews.
8-1589456-1	1589455	SSM025PC2DC012Q	Dualobe, 1 row, metal, 25 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches, 1.2 captive jackscrews.
8-1589456-2	1589455	SSG005PC2DC006N	Dualobe, 1 row, gold, 5 position, plug, 30 AWG 7 strand, color coded PTFE wire, 6 inches, 1.0 captive jackscrews.
8-1589456-3	1589455	SSM025PC2DM024N	Dualobe, 1 row, metal, 25 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 24 inches, 1.0 captive jackscrews.
8-1589456-4	1589455	SSM037PC2DM024N	Dualobe, 1 row, metal, 37 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 24 inches, 1.0 captive jackscrews.
8-1589456-5	1589455	SSL025PC0DC012M	Dualobe, 1 row, LCP, 25 position, plug, 28 AWG solid, color coded PTFE wire, 12 inches, 1.0 non-captive jackscrews.
8-1589456-6	1589455	SSM037PC4DX018N	Dualobe, 1 row, metal, 37 position, plug, 34 AWG 7 strand, white PTFE wire, 18 inches, 1.0 captive jackscrews.
8-1589456-7	1589455	SSM009PC2DCC02N	Dualobe, 1 row, metal, 9 position, plug, 30 AWG 7 strand, color coded PTFE wire, 2 meters, 1.0 captive jackscrews.
8-1589456-8	1589455	SSM009PC2DC084N	Dualobe, 1 row, metal, 9 position, plug, 30 AWG 7 strand, color coded PTFE wire, 84 inches, 1.0 captive jackscrews.
8-1589456-9	1589455	SSM005PC0DX024N	Dualobe, 1 row, metal, 5 position, plug, 28 AWG solid, white PTFE wire, 24 inches, 1.0 captive jackscrews.
9-1589456-0	1589455	SSS005PC0DX024N	Dualobe, 1 row, stainless, 5 position, plug, 28 AWG solid, white PTFE wire, 24 inches, 1.0 captive jackscrews.
9-1589456-1	1589455	SSM025PC2DC024N	Dualobe, 1 row, metal, 25 position, plug, 30 AWG 7 strand, color coded PTFE wire, 24 inches, 1.0 captive jackscrews.
9-1589456-2	1589455	SSL009PC2DC012Q	Dualobe, 1 row, LCP, 9 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches, 1.2 captive jackscrews.
9-1589456-3	1589455	SSM051PC2DCC30N	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, color coded PTFE wire, 30 centimeters, 1.0 captive jackscrews.
9-1589456-4	1589455	SSM015PC2DM012N	Dualobe, 1 row, metal, 15 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 12 inches, 1.0 captive jackscrews.
9-1589456-5	1589455	SSM037PC2DC012Q	Dualobe, 1 row, metal, 37 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches, 1.2 captive jackscrews.
9-1589456-6	1589455	SSL025PC2DC018N	Dualobe, 1 row, LCP, 25 position, plug, 30 AWG 7 strand, color coded PTFE wire, 18 inches, 1.0 captive jackscrews.
9-1589456-7	1589455	SSM005PC2DCC20N	Dualobe, 1 row, metal, 5 position, plug, 30 AWG 7 strand, color coded PTFE wire, 20 centimeters, 1.0 captive jackscrews.
9-1589456-8	1589455	SSM037PC2DTC30N	Dualobe, 1 row, metal, 37 position, plug, 30 AWG 7 strand, white ETFE M22759/33 wire, 30 centimeters, 1.0 captive jackscrews.
9-1589456-9	1589455	SSM025PC2DM018Q	Dualobe, 1 row, metal, 25 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 18 inches, 1.2 captive jackscrews.
1589827-1	1589455	SSL025PC2DC024M	Dualobe, 1 row, LCP, 25 position, plug, 30 AWG 7 strand, color coded PTFE wire, 24 inches, 1.0 non-captive jackscrews.
1589827-2	1589455	SSL015PC2DC012M	Dualobe, 1 row, LCP, 15 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches, 1.0 non-captive jackscrews.
1589827-3	1589455	SSL015PC2DC003N	Dualobe, 1 row, LCP, 15 position, plug, 30 AWG 7 strand, color coded PTFE wire, 3 inches, 1.0 captive jackscrews.
1589827-4	1589455	SSM051PC2DX012Q	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, white PTFE wire, 12 inches, 1.2 captive jackscrews.
1589827-5	1589455	SSL015PC2DC036N	Dualobe, 1 row, LCP, 15 position, plug, 30 AWG 7 strand, color coded PTFE wire, 36 inches, 1.0 captive jackscrews.
1589827-6	1589455	SSL015PC0DC012N	Dualobe, 1 row, LCP, 15 position, plug, 28 AWG solid, color coded PTFE wire, 12 inches, 1.0 captive jackscrews.
1589827-7	1589455	SSM009PC0DC012N	Dualobe, 1 row, metal, 9 position, plug, 28 AWG solid, color coded PTFE wire, 12 inches, 1.0 captive jackscrews.
1589827-8	1589455	SSL015PC2DC016N	Dualobe, 1 row, LCP, 15 position, plug, 30 AWG 7 strand, color coded PTFE wire, 16 inches, 1.0 captive jackscrews.



7-1589827-8	1589455	SSL025PC2DC030N	Dualobe, 1 row, LCP, 25 position, plug, 30 AWG 7 strand, color coded PTFE wire, 30 inches, 1.0 captive jackscrews.
7-1589827-9	1589455	SSM051PC2DC012Q	Dualobe, 1 row, metal, 51 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches, 1.2 captive jackscrews.
8-1589827-0	1589455	SSL009PC0DM006N	Dualobe, 1 row, LCP, 9 position, plug, 28 AWG solid, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 6 inches, 1.0 captive jackscrews.
8-1589827-1	1589455	SSM005PC0DC024N	Dualobe, 1 row, metal, 5 position, plug, 28 AWG solid, color coded PTFE wire, 6 inches, 1.0 captive jackscrews.
8-1589827-2	1589455	SSM009PC0DM012N	Dualobe, 1 row, metal, 9 position, plug, 28 AWG solid, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 12 inches, 1.0 captive jackscrews.