











7-1589777-8	1589476	STM037SC2DX036N	Dualobe, 2 row, metal, 37 position, receptacle, 30 AWG 7 strand, white PTFE wire, 36 inches, thread for 1.0 jackscrews.
7-1589777-9	1589476	STM025SC2DX036N	Dualobe, 2 row, metal, 25 position, receptacle, 30 AWG 7 strand, white PTFE wire, 36 inches, thread for 1.0 jackscrews.
8-1589777-0	1589476	STM051SC2DC240N	Dualobe, 2 row, metal, 51 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 240 inches, thread for 1.0 jackscrews.
8-1589777-1	1589476	STL051SC2DC240N	Dualobe, 2 row, LCP, 51 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 240 inches, thread for 1.0 jackscrews.
8-1589777-2	1589476	STM015SC2DC030N	Dualobe, 2 row, metal, 15 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 30 inches, thread for 1.0 jackscrews.
8-1589777-3	1589476	STM051SC2DT024Q	Dualobe, 2 row, metal, 51 position, receptacle, 30 AWG 7 strand, white ETFE M22759/33 wire, 24 inches, thread for 1.2 jackscrews.
8-1589777-4	1589476	STS009SC2DM012N	Dualobe, 2 row, stainless, 9 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 12 inches, thread for 1.0 jackscrews.
8-1589777-5	1589476	STM015SC2DC018Q	Dualobe, 2 row, metal, 15 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 18 inches, thread for 1.2 jackscrews.
8-1589777-6	1589476	STM015SC2DM018N	Dualobe, 2 row, metal, 15 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 18 inches, thread for 1.0 jackscrews.
8-1589777-7	1589476	STM009SC2DM018Q	Dualobe, 2 row, metal, 9 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 18 inches, thread for 1.2 jackscrews.
8-1589777-8	1589476	STM015SC2DM018Q	Dualobe, 2 row, metal, 15 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 18 inches, thread for 1.2 jackscrews.
8-1589777-9	1589476	STM065SC2DM018Q	Dualobe, 2 row, metal, 65 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 18 inches, thread for 1.2 captive jackscrews.
9-1589777-0	1589476	STM025SC0DM012Q	Dualobe, 2 row, metal, 25 position, receptacle, 28 AWG solid, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 12 inches, thread for 1.2 jackscrews.
9-1589777-1	1589476	STM015SC2DC020Q	Dualobe, 2 row, metal, 15 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 20 inches, thread for 1.2 jackscrews.
9-1589777-2	1589476	STL015SC2DC001N	Dualobe, 2 row, LCP, 15 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 1 inch, thread for 1.0 jackscrews.
9-1589777-3	1589476	STL025SC4DX030HN	Dualobe, 2 row, LCP, 25 position, receptacle, 34 AWG 7 strand, white PTFE wire, 30 inches, 1.0 X .160 mounting screws, thread for 1.0 jackscrews.
9-1589777-4	1589476	STM065SC2DX012N	Dualobe, 2 row, metal, 65 position, white PTFE wire per M16878/6, 12 inches, thread for 1.0 jackscrews
9-1589777-5	1589476	STM065SC3DM012Q	Dualobe, 2 row, metal, 65 position, receptacle, 32 AWG 7 strand, color coded PTFE, MIL-STD-681 wire, 12 inches, thread for 1.2 jackscrews.