

TE P/N	TE CD	Nanonics P/N	Part Description
1589490-1	1589490	STL015B2N	Dualobe, 2 row, LCP, 15 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.0 captive jackscrews.
1589490-2	1589490	STL025B2	Dualobe, 2 row, LCP, 25 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe.
1589490-3	1589490	STM015B2N	Dualobe, 2 row, metal, 15 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.0 captive jackscrews.
1589490-4	1589490	STM025B2N	Dualobe, 2 row, metal, 25 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.0 captive jackscrews.
1589490-5	1589490	STM037B2N	Dualobe, 2 row, metal, 37 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.0 captive jackscrews.
1589490-6	1589490	STM051B2N	Dualobe, 2 row, metal, 51 position, plug, horizontal mount, surface termination, .020 foot tin/lead leadframe, 1.0 captive jackscrews.
1589490-7	1589490	STM051B2N3	OBSOLETE
1589490-8	1589490	STM051B2Q	Dualobe, 2 row, 51 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.2 captive jackscrews.
1589490-9	1589490	STM065B2Q	Dualobe, 2 row, metal, 65 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.2 captive jackscrews.
1-1589490-0	1589490	STM065B2N	Dualobe, 2 row, metal, 65 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.0 captive jackscrews.
1-1589490-1	1589490	STL025B2N	Dualobe, 2 row, LCP, 25 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.0 captive jackscrews.
1-1589490-2	1589490	STM009B2N	Dualobe, 2 row, metal, 9 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.0 captive jackscrews.
1-1589490-3	1589490	STL037B2M	Dualobe, 2 row, LCP, 37 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.0 non-captive jackscrews.
1-1589490-4	1589490	STM037B2M	Dualobe, 2 row, metal, 37 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.0 non-captive jackscrews.
1-1589490-5	1589490	STM037B2	Dualobe, 2 row, metal, 37 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe.
1-1589490-6	1589490	STM025B2Q	Dualobe, 2 row, metal, 25 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.2 captive jackscrews.
1-1589490-7	1589490	STM037B2Q	Dualobe, 2 row, metal, 37 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.2 captive jackscrews.
1-1589490-8	1589490	STL015B2M	Dualobe, 2 row, LCP, 15 position, plug, horizontal mount, surface termination, .020 foot, tin/lead leadframe, 1.0 non-captive jackscrews.