

TE P/N	TE CD	Nanonics P/N	Part Description
7-1589671-5	1589797	JSL037PD2GXC02N	Jumper, 1 row, LCP, 37 position, plug to plug, low to hi in row, FEP ribbon cable, 2 centimeters, 1.0 captive jackscrews.
7-1589671-7	1589797	JSL051PD2GXC10N	Jumper, 1 row, LCP, 51 position, plug to plug, low to hi in row, FEP ribbon cable, 10 centimeters, 1.0 captive jackscrews.
7-1589671-8	1589797	JSL051PD2GXC17N	Jumper, 1 row, LCP, 51 position, plug to plug, low to hi in row, FEP ribbon cable, 17 centimeters, 1.0 captive jackscrews.
7-1589671-9	1589797	JSL051PD2GXC22N	Jumper, 1 row, LCP, 51 position, plug to plug, low to hi in row, FEP ribbon cable, 22 centimeters, 1.0 captive jackscrews.
8-1589671-0	1589797	JSL051PD2GXC30N	Jumper, 1 row, LCP, 51 position, plug to plug, low to hi in row, FEP ribbon cable, 30 centimeters, 1.0 captive jackscrews.
8-1589671-1	1589797	JSL051PD2GXC75N	Jumper, 1 row, LCP, 51 position, plug to plug, low to hi in row, FEP ribbon cable, 75 centimeters, 1.0 captive jackscrews.
8-1589671-2	1589797	JSL051PD2GXC80N	Jumper, 1 row, LCP, 51 position, plug to plug, low to hi in row, FEP ribbon cable, 80 centimeters, 1.0 captive jackscrews.
1589672-6	1589797	JSM015PD2DCC02N	Jumper, 1 row, metal, 15 position, plug to plug, low to high, 30 AWG 7 strand, color coded PTFE wire, 2 centimeters, 1.0 captive jackscrews.
3-1589672-3	1589797	JSM037PD2GXC10N	Jumper, 1 row, metal, 37 position, plug to plug, low to hi, 30AWG 7 strand, FEP ribbon cable, 10 centimeters, 1.0 captive jackscrews.
4-1589672-7	1589797	JSM051PD2GXC10N	Jumper, 1 row, metal, 51 position, plug to plug, low to hi in row, FEP ribbon cable, 10 centimeters, 1.0 captive jackscrews.
4-1589672-8	1589797	JSM051PD2GXC12	Jumper, 1 row, metal, 51 position, plug to plug, low to hi, 30 AWG 7 strand, FEP ribbon cable, 12 centimeters.
4-1589672-9	1589797	JSM051PD2GXC12N	Jumper, 1 row, metal, 51 position, plug to plug, low to hi, 30 AWG 7 strand, FEP ribbon cable, 12 centimeters, 1.0 captive jackscrews.
5-1589672-0	1589797	JSM051PD2GXC15N	Jumper, 1 row, metal, 51 position, plug to plug, low to hi in row, FEP ribbon cable, 15 centimeters, 1.0 captive jackscrews.
5-1589672-1	1589797	JSM051PD2GXC17N	Jumper, 1 row, metal, 51 position, plug to plug, low to hi in row, 30AWG 7 strand FEP ribbon cable, 17 centimeters, 1.0 captive jackscrews.
5-1589672-2	1589797	JSM051PD2GXC50N	Jumper, 1 row, metal, 51 position, plug to plug, low to hi, 30AWG 7 strand FEP ribbon cable, 50 centimeters, 1.0 captive jackscrews.
4-1589699-8	1589797	JSL015PD2DX002N	Jumper, 1 row, LCP, 15 position, plug to plug, low to hi, 30AWG 7 strand, white PTFE wire, 2 inches, 1.0 captive jackscrews.
2-1589735-3	1589797	JSM015PP2DCC23N	Jumper, 1 row, metal, 15 position, plug to plug, 1 to 1, 30AWG 7 strand, color coded PTFE wire, 23 centimeters, 1.0 captive jackscrews.
1589797-1	1589797	JSM037PD2GXC05N	Jumper, 1 row, metal, 37 position, plug to plug, low to hi, 30AWG 7 strand, FEP ribbon cable, 5 centimeters, 1.0 captive jackscrews.
1589797-2	1589797	JSM037PD2GXC02N	Jumper, 1 row, metal, 37 position, plug to plug, low to hi, 30AWG 7 strand, FEP ribbon cable, 2 centimeters, 1.0 captive jackscrews.
1589797-3	1589797	JSM015PD2GXC05N	Jumper, 1 row, metal, 15 position, plug to plug, low to high, 30 AWG 7 strand, FEP ribbon cable, 5 centimeters, 1.0 captive jackscrews.
1589797-4	1589797	JSM025PD2GXC02N	Jumper, 1 row, metal, 25 position, plug to plug, low to hi, 30 AWG 7 strand, FEP ribbon cable, 2 centimeters, 1.0 captive jackscrews.
1589797-5	1589797	JSM037PD2GXC02Q	Jumper, 1 row, metal, 37 position, plug to plug, low to hi, 30 AWG 7 strand, FEP ribbon cable, 2 centimeters, 1.2 captive jackscrews.
1589797-6	1589797	JSM009PD2DCC25N	Jumper, 1 row, metal, 9 position, plug to plug, low to hi, 30 AWG 7 strand, color coded PTFE wire, 25 centimeters, 1.0 captive jackscrews.
1589797-7	1589797	JSM009PD2DCC17N	Jumper, 1 row, metal, 9 position, plug to plug, low to hi, 30 AWG 7 strand, color coded PTFE wire, 17 centimeters, 1.0 captive jackscrews.
1589797-8	1589797	JSM015PD2DCC23N	Jumper, 1 row, metal, 15 position, plug to plug, low to hi, 30 AWG 7 strand, color coded PTFE wire, 23 centimeters, 1.0 captive jackscrews.
1589797-9	1589797	JSM015PD2DCC27N	Jumper, 1 row, metal, 15 position, plug to plug, low to hi, 30 AWG 7 strand, color coded PTFE wire, 27 centimeters, 1.0 captive jackscrews.
1-1589797-0	1589797	JSM037PD2DCC10Q	Jumper, 1 row, metal, 37 position, plug to plug, low to hi, 30 AWG 7 strand, color coded PTFE wire, 10 centimeters, 1.2 captive jackscrews.
1-1589797-1	1589797	JSM037PD2DCC11Q	Jumper, 1 row, metal, 37 position, plug to plug, low to hi, 30 AWG 7 strand, color coded PTFE wire, 11 centimeters, 1.2 captive jackscrews.
1-1589797-2	1589797	JSM037PD2DCC15Q	Jumper, 1 row, metal, 37 position, plug to plug, low to hi, 30 AWG 7 strand, color coded PTFE wire, 15 centimeters, 1.2 captive jackscrews.
1-1589797-3	1589797	JSM015PD2DCC04N	Jumper, 1 row, metal, 15 position, plug to plug, low to high, 30 AWG 7 strand, color coded PTFE wire, 4 centimeters, 1.0 captive jackscrews.
1-1589797-4	1589797	JSM025PD2DCC20N	Jumper, 1 row, metal, 25 position, plug to plug, low to high, 30 AWG 7 strand, color coded PTFE wire, 20 centimeters, 1.0 captive jackscrews.
1-1589797-5	1589797	JSM025PD2DCC10N	Jumper, 1 row, metal, 25 position, plug to plug, low to high, 30 AWG 7 strand, color coded PTFE wire, 10 centimeters, 1.0 captive jackscrews.
1-1589797-6	1589797	JSM025PD2DCC05N	Jumper, 1 row, metal, 25 position, plug to plug, low to high, 30 AWG 7 strand, color coded PTFE wire, 5 centimeters, 1.0 captive jackscrews.