

TE P/N	TE CD	Nanonics P/N	Part Description
1589809-1	1589809	STM025W6SN	Dualobe, 2 row, metal, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, gold leadframe, 1.0 x .160 mounting screw w/2 standoffs, thread for 1.0 jackscrews.
1589809-2	1589809	STM051W6SN	Dualobe, 2 row, metal, 51 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, gold leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1589809-3	1589809	STL015W6SN	Dualobe, 2 row, LCP, 15 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, gold leadframe, 1.0 x .160 mounting screw w/2 standoffs, thread for 1.0 jackscrews.
1589809-4	1589809	STL025W6SN	Dualobe, 2 row, LCP, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, gold leadframe, 1.0 x .160 mounting screw w/2 standoffs, thread for 1.0 jackscrews.
1589809-5	1589809	STM051W6CN	Dualobe, 2 row, metal, 51 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, gold leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1589809-6	1589809	STM065W6DN	Dualobe, 2 row, metal, 65 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, gold leadframe, 1.2 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1589809-7	1589809	STM025W6CN	Dualobe, 2 row, metal, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, gold leadframe, 1.0 x .200 mounting screw w/2 standoffs, thread for 1.0 jackscrews.
1589809-8	1589809	STL025W6DQ	Dualobe, 2 row, LCP, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, gold leadframe, 1.2 x .160 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.
1589809-9	1589809	STM015W6AN	Dualobe, 2 row, metal, 15 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, gold leadframe, 1.2 x .160 mounting screw, thread for 1.0 jackscrews.
1-1589809-0	1589809	STM015W6DQ	Dualobe, 2 row, metal, 15 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, gold leadframe, 1.2 x .160 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.
1-1589809-1	1589809	STM025W6AN	Dualobe, 2 row, metal, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, gold leadframe, 1.2 x .160 mounting screw, thread for 1.0 jackscrews.
1-1589809-2	1589809	STM025W6DQ	Dualobe, 2 row, metal, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, gold leadframe, 1.2 x .160 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.
1-1589809-3	1589809	STM037W6DQ	Dualobe, 2 row, metal, 37 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, gold leadframe, 1.2 x .160 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.
1-1589809-4	1589809	STM051W6DQ	Dualobe, 2 row, metal, 51 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, gold leadframe, 1.2 x .160 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.
1-1589809-5	1589809	STM065W6AQ	Dualobe, 2 row, metal, 65 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, gold leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
1-1589809-6	1589809	STM037W6CN	Dualobe, 2 row, metal, 37 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, gold leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1-1589809-7	1589809	STM037W6HN	Dualobe, 2 row, metal, 37 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, gold leadframe, 1.0 x .160 mounting screws, thread for 1.0 jackscrews.