



Nanonics Standard Catalog Part Number Cross-Reference

Revision 1

TE P/N	TE CD	Nanonics P/N	Part Description
1589816-1	1589816	STM037T4KN	Dualobe, 2 row, metal, 37 position, receptacle, vertical mount, surface termination, .020 foot gold leadframe, 1.0 x .200 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
1589816-2	1589816	STM051T4KN	Dualobe, 2 row, metal, 51 position, receptacle, vertical mount, surface termination, .020 foot, gold leadframe, 1.0 x .200 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
1589816-3	1589816	STM037T4HN	Dualobe, 2 row, metal, 37 position, receptacle, vertical mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589816-4	1589816	STM037T4PQ	Dualobe, 2 row, metal, 37 position, receptacle, vertical mount, surface termination, .020 foot, gold leadframe, 1.2 x .200 mounting screw w/ 4 standoffs, thread for 1.2 jackscrews.
1589816-5	1589816	STM051T42KN	Dualobe, 2 row, metal, 51 position, receptacle, vertical mount, surface termination, 2 side exit, .020 extended leads, gold leadframe, 1.0 x .200 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
1589816-6	1589816	STM051T42N	Dualobe, 2 row, metal, 51 position, receptacle, vertical mount, surface termination, 2 side exit, .020 extended leads, gold leadframe, thread for 1.0 jackscrews.
1589816-7	1589816	STL025T4PQ	Dualobe, 2 row, LCP, 25 position, receptacle, vertical mount, surface termination, .020 foot, gold leadframe, 1.2 x .200 mounting screw w/ 4 standoffs, thread for 1.2 jackscrews.
1589816-8	1589816	STL051T4PQ	Dualobe, 2 row, LCP, 51 position, receptacle, vertical mount, surface termination, .020 foot, gold leadframe, 1.2 x .200 mounting screw w/ 4 standoffs, thread for 1.2 jackscrews.
1589816-9	1589816	STM037T4SN	Dualobe, 2 row, metal, 37 position, receptacle, vertical mount, surface termination, .020 foot, gold leadframe, 1.0 x .160 mounting screw, w/2 standoffs, thread for 1.0 jackscrews.