

TE P/N	TE CD	Nanonics P/N	Part Description
1-1589578-8	1589886	JX080PP2RG012	Jumper, coax, 50 ohm, 8 position, plug to plug, 1 to 1, 30 AWG RG-178 cable, 12 inches.
1-1589676-1	1589886	JX030PP2RG012N	Jumper, coax, 50 ohm, 3 position, plug to plug, 1 to 1, 30 AWG RG-178 coaxial cable, 12 inches, 1.0 captive jackscrews.
1-1589676-2	1589886	JX030PP2RG015N	Jumper, coax, 50 ohm, 3 position, plug to plug, 1 to 1, 30 AWG RG-178 coaxial cable, 15 inches, 1.0 captive jackscrews.
5-1589699-2	1589886	JX010PP2RGC05N	Jumper, coax, 50 ohm, 1 position, plug to plug, 1 to 1, 30 AWG RG-178 coaxial cable, 5 centimeters, 1.0 captive jackscrews.
1-1589789-1	1589886	JX020PP2RG168N	Jumper, coax, 50 ohm, 2 position, plug to plug, 1 to 1, 30 AWG RG-178 cable, 168 inches, 1.0 captive jackscrews.
9-1589789-5	1589886	JX060PP2RG036N	Jumper, coax, 50 ohm, 6 position, plug to plug, 1 to 1, 30 AWG RG-178 coaxial cable, 36 inches, 1.0 captive jackscrews.
3-1589848-3	1589886	JX080PP2RG012N	Jumper, coax, 50 ohm, 8 position, plug to plug, 1 to 1, 30 AWG RG-178 cable, 12 inches, 1.0 captive jackscrews.
5-1589848-0	1589886	JX060PP2RG018N	Jumper, coax, 50 ohm, 6 position, plug to plug, 1 to 1, 30 AWG RG-178 coaxial cable, 18 inches, 1.0 captive jackscrews.
5-1589848-1	1589886	JX080PP2RG018N	Jumper, coax, 50 ohm, 8 position, plug to plug, 1 to 1, 30 AWG RG-178 cable, 18 inches, 1.0 captive jackscrews.
6-1589848-7	1589886	JX060PP2RG024N	Jumper, coax, 50 ohm, 6 position, plug to plug, 1 to 1, 30 AWG RG-178 coaxial cable, 24 inches, 1.0 captive jackscrews.
6-1589848-8	1589886	JX080PP2RG024N	Jumper, coax, 50 ohm, 8 position, plug to plug, 1 to 1, 30 AWG RG-178 cable, 24 inches, 1.0 captive jackscrews.
1589886-1	1589886	JX080PP2RG036N	Jumper, coax, 50 ohm, 8 position, plug to plug, 1 to 1, 30 AWG RG-178 cable, 36 inches, 1.0 captive jackscrews.
1589886-2	1589886	JX060PP2RG027N	Jumper, coax, 50 ohm, 6 position, plug to plug, 1 to 1, 30 AWG RG-178 coaxial cable, 27 inches, 1.0 captive jackscrews.
1589886-3	1589886	JX080PP2RG040N	Jumper, coax, 50 ohm, 8 position, plug to plug, 1 to 1, 30 AWG RG-178 cable, 40 inches, 1.0 captive jackscrews.
1589886-4	1589886	JX040PP2RG036Q	Jumper, coax, 50 ohm, 4 position, plug to plug, 1 to 1, 30 AWG RG-178 coaxial cable, 36 inches, 1.2 captive jackscrews.
1589886-5	1589886	JX040PP2RG024N	Jumper, coax, 50 ohm, 4 position, plug to plug, 1 to 1, 30 AWG RG-178 coaxial cable, 24 inches, 1.0 captive jackscrews.
1589886-6	1589886	JX020PP2RG018N	Jumper, coax, 50 ohm, 2 position, plug to plug, 1 to 1, 30 AWG RG-178 cable, 18 inches, 1.0 captive jackscrews.
1589886-7	1589886	JX060PP2RG030N	Jumper, coax, 50 ohm, 6 position, plug to plug, 1 to 1, 30 AWG RG-178 coaxial cable, 30 inches, 1.0 captive jackscrews.
1589886-8	1589886	JX080PP2RG030N	Jumper, coax, 50 ohm, 8 position, plug to plug, 1 to 1, 30 AWG RG-178 cable, 30 inches, 1.0 captive jackscrews.
1589886-9	1589886	JX040PP2RGC10M	Jumper, coax, 50 ohm, 4 position, plug to plug, 1 to 1, 30 AWG RG-178 coaxial cable, 10 centimeters, 1.0 non-captive jackscrews.
1-1589886-0	1589886	JX040PP2RGM01M	Jumper, coax, 50 ohm, 4 position, plug to plug, 1 to 1, 30 AWG RG-178 coaxial cable, 1 meter, 1.0 non-captive jackscrews.
1-1589886-1	1589886	JX030PP2RGC10N	Jumper, coax, 50 ohm, 3 position, plug to plug, 1 to 1, 30 AWG RG-178 coaxial cable, 10 centimeters, 1.0 captive jackscrews.
1-1589886-2	1589886	JX030PP2RGC09N	Jumper, coax, 50 ohm, 3 position, plug to plug, 1 to 1, 30 AWG RG-178 coaxial cable, 9 centimeters, 1.0 captive jackscrews.
1-1589886-3	1589886	JX030PP2RGC08N	Jumper, coax, 50 ohm, 3 position, plug to plug, 1 to 1, 30 AWG RG-178 coaxial cable, 8 centimeters, 1.0 captive jackscrews.
1-1589886-4	1589886	JX020PP2RGC15Q	Jumper, coax, 50 ohm, 2 position, plug to plug, 1 to 1, 30 AWG RG-178 coaxial cable, 15 centimeters, 1.2 captive jackscrews.
1-1589886-5	1589886	JX080PP2RG028N	Jumper, coax, 50 ohm, 8 position, plug to plug, 1 to 1, 30 AWG RG-178 cable, 28 inches, 1.0 captive jackscrews.
1-1589886-6	1589886	JX080PP3CW024N	Jumper, coax, 50 ohm, 8 position, plug to plug, 1 to 1, 32 AWG FEP insulated coaxial cable, 24 inches, 1.0 captive jackscrews.