




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
AF	50	E3		REVISED PER ECR-21-124606	21DEC2021	PC TD	



- SPECIFICATIONS:
MAGNET WIRE #23 - #20 AWG,
0.58(.023)-0.81(.032) DIA. COPPER
UP TO TWO WIRES OF THE SAME
SIZE MAY BE TERMINATED BY A
SINGLE TERMINAL.
- POCKET RECOMMENDATION: #1601425.
- TERMINAL APPLICATION TO COMPLY WITH
TYCO ELECTRONICS SPECIFICATION 114-13166 FIGURE 6.



-	-	-
-	-	-
-	-	-
UNPLATED	059-001-000	4-1601142-1
UNPLATED	159-001-000	2-1601142-1
UNPLATED	159-002-000	1601142-1
FINISH	REFERENCE PART NUMBER	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.WELLER 11JAN2002
DIMENSIONS: mm [INCHES]		CHK M.FEHER 11JAN2002
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K.RANDOLPH 11JAN2002
0 PLC ± -	1 PLC ± 0.25 [.010]	NAME
2 PLC ± 0.13 [.005]	3 PLC ± -	PRODUCT SPEC
4 PLC ± -	ANGLES ± 2°	108-2085
MATERIAL BRASS, FULL HARD	FINISH SEE TABLE	APPLICATION SPEC
WEIGHT -		SIZE A2
CUSTOMER DRAWING		CAGE CODE 00779
SCALE 5:1		DRAWING NO C=1601142
SHEET 1 OF 1		RESTRICTED TO -
REV E3		