


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - TE Connectivity Ltd. ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	A2	OBSOLETE PN 4-160997-1	22MAR2018	SH NG

NOTE:
 1 RANGE: Ø24 MAX.
 2 MIN. TENSILE STRENGTH 200N.
 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



	1000	BLACK	POLYAMIDE 6.6	4-160997-2
OBSOLETE	1000	NATURAL	POLYAMIDE 6.6	4-160997-1
OBSOLETE	100	BLACK	POLYAMIDE 6.6	2-160997-2
3	100	NATURAL	POLYAMIDE 6.6	2-160997-1
	QTY	FINISH	MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	DWN J.V.D.HEIJDEN. 27-02-92 CHK R.VOS. APVD L.V.SOEST. PRODUCT SPEC APPLICATION SPEC WEIGHT	TE Connectivity CABLE TY.	
MATERIAL	FINISH	SIZE A3	CAGE CODE 00779	DRAWING NO C-160997
		CUSTOMER DRAWING		RESTRICTED TO
		SCALE -	SHEET 1 OF 1	REV A2