

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2002

BY TYCO ELECTRONICS CORPORATION.





ALL RIGHTS RESERVED.

LOC
J

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED FJBO-0113-05	3FEB05	L.Z	I.E





NOTES

1. MATERIAL:

REC HOUSING: THERMO PLASTIC UL94V-0
REC CONTACT: COPPER ALLOY, Sn PLATING

2. APPLICABLE WIRE:

AWG36(7/0.05) INSULATION DIAMETER ϕ 0.39 \pm 0.02



0.08	NATURAL	12.3	12.8	11.2	15	1-1674502-5
0.07	NATURAL	11.5	12	10.4	14	1-1674502-4
0.06	NATURAL	9.9	10.4	8.8	12	1-1674502-2
0.05	NATURAL	9.1	9.6	8	11	1-1674502-1
0.04	NATURAL	8.3	8.8	7.2	10	1-1674502-0
0.04	NATURAL	6.7	7.2	5.6	8	1674502-8
0.02	NATURAL	3.5	4	2.4	4	1674502-4
0.01	NATURAL	1.9	2.4	0.8	2	1674502-2
WEIGHT(g)	COLOR	C	B	A	POSITION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN J.TSUJI 09APR03

CHK S.KAJINUMA 09APR03

APVD Y.YAMAMOTO 09APR03

PRODUCT SPEC

108-5830

APPLICATION SPEC

114-5319

WEIGHT SEE TABLE

CUSTOMER DRAWING



Tyco Electronics AMP K.K.
Kawasaki, Japan

NAME

RECEPTACLE ASSEMBLY

0.8mm PITCH WIRE TO BOARD

MICRO TERMINATION (MT) CONNECTOR


SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C=1674502

SCALE 10:1 SHEET 1 OF 1 REV B

DIMENSIONS:

MM



TOLERANCES UNLESS OTHERWISE SPECIFIED:

Ø-PLG	±	
1-PLG	±	±0.3
2-PLG	±	±3'
3-PLG	±	
4-PLG	±	
ANGLES	±	

MATERIAL



FINISH

