




注記;




- 1 一般公差 ; ±0.4
- 2 製品規格 ; 108-1031, 108-1053
- 3 取引適用規格 ; 114-1010
- 4 本製品は 350570-3 の ReReeling 品である。  
パラ状接触子型番 174273-2 と型番 350689-3  
を同様である。

NOTES;

- 1 GENERAL TOLERANCE ; ±0.4
- 2 PRODUCT SPEC ; 108-1031, 108-1053
- 3 APPLICATION SPEC ; 114-1010
- 4 This product is ReReeling of 350570-3.  
IN THE SAME WAY WITH P/N 174273-2 AND P/N 350689-3



SECTION A-A



SECTION B-B

174273-2	MINI	PRE-TIN, X-222	PH BR3	174273-1
LOOSE PIECE	APPLICATOR TYPE	FINISH	MATERIAL	PART NO

© 1987 年 日本エー・エム・ピー株式会社 AMP社の諸製品は特許又は特許出願中		© 1987 BY AMP (Japan) LTD. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND OR PATENTS PENDING		<b>tyco</b> <b>Electronics</b>		Tyco Electronics AMP K.K. Kawasaki, Japan	
総合電線断面積(WIRE RANGE) 0.20 0.89 mm <sup>2</sup> (AWG 24~18)		絶縁外径 (INSULATION DIA.) 1.92 2.54 mm		名称 (NAME) SOCKET UNIVERSAL MATE-N-LOK			
材料 (MATERIAL) SEE TABLE		仕上 (FINISH) SEE TABLE		公差 10以下 ±0.2 10を超え 30以下 ±0.25 30を超え 100以下 ±0.3 角 度 ±°		SIZE <b>A3 J</b>	番号 (NO.) <b>C-174273</b>
A	REVISED FJD0-0356-04	Y.Y	D.M	30SEP '04	DR	J. Futatabi	3-31-97
0	RELEASED J-974677				DE	J. Futatabi	
LTR	変更 (REVISION RECORD)	DR	CHK	DATE	APP	J. Futatabi	
				R 度 (SCALE) ++		REV. A	SHEET 1 OF 1

PRINT DIST 単位: ㎜ DIMENSIONS IN MM. DO NOT SCALE PRINT