



NUMBER
C-176392

(3rd ANGLE PROJECTION)

METRIC

DIMENSIONS IN MM. DO NOT SCALE PRINT

PRINT DIST



- NOTES:
- APPLICABLE WIRE SIZE : AWG# 28-26
(UL1571, UL1061)
INSULATION DIA RANGE : 0.83-1.05
 - MATERIAL :
HOUSING : PBT(G.F)UL94V-0
CONTACT : GOLD PLATED PHOS-BRONZE (0.0002mm)
 - PRODUCT SPEC : 108-5218
 - APPLICATION SPEC : 114-5104

1-176392-5	15	28	30.8	32
1-176392-4	14	26	28.8	30
1-176392-3	13	24	26.8	28
1-176392-2	12	22	24.8	26
1-176392-1	11	20	22.8	24
1-176392-0	10	18	20.8	22
-9	9	16	18.8	20
-8	8	14	16.8	18
-7	7	12	14.8	16
-6	6	10	12.8	14
-5	5	8	10.8	12
-4	4	6	8.8	10
-3	3	-AS SHOWN-		
176392-2	2	-AS SHOWN-		
NATURAL	POS			
PART No.		A	B	C

				Copyright ©1999		Copyright ©1999		AMP MANUFACTURING (SINGAPORE) PTE. LTD. ALL RIGHTS RESERVED.		AMP		AMP MANUFACTURING (SINGAPORE) PTE. LTD.	
				(WIRE RANGE)	(INSULATION DIA.)	(NAME)		MT REC HOUSING ASS'Y (AMP CT CONNECTOR 2mm PITCH) (GOLD PLATING TYPE)					
				NOTE 1 mm ² (AWG -)	NOTE 1 mm ϕ								
				(MATERIAL)	(FINISH)	GENERAL TOLERANCE		SIZE	LOC	(No.)			
				NOTE 2	---			A3	DY	C-176392			
B	REVISED (FP00-0394-01)	LWY	TLP	18OCT 2001	DR. 23/AUG/'99	DE. 23/AUG/'99	0<* < 10 : ±0.2						
A	REDRAWN (FJ00-1083-99)	J.T	J.T	25/AUG '99	J.TSUJI	J.TSUJI	10<* < 30 : ±0.25						
LTR	(REVISION RECORD)	DR	CHK	DATE	CHK. 25/AUG/'99	APP. 18OCT01	30<* < 100 : ±0.3		(SCALE)	REV.	SHEET		
					J.TANIGAWA	WL CHOO	ANGLES : ±3°		4-1	B	1 OF 1		