


P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REVISED	FJBO-0346-03	28APR03	T.K Y.Y



- 1 嵌合相手型番: 179394,179867
- 2 材料:
リセハウジング : 6T NYLON,GF30%
リセコンタクト: 銅合金 (t=0.25mm),ニッケル下地、鍍めっき
- 3 全てのタイン部のバラツキは 0.15mm MAX.

28.0	31.8	28.0	30	3-179395-0
20.0	23.8	20.0	22	2-179395-2
4.0	7.8	4.0	6	179395-6
C	B	A	極数 Pos.	型番 PART NO.

- 1 MATING COUNTER PART NUMBER: 179394,179867
- 2 MATERIAL:
HOUSING : 6T NYLON,GF30%
REC CONTACT: COPPER-ALLOY (t=0.25mm)
TIN PLATING, Ni UNDER PL. ALL OVER
- 3 MISALIGNMENT BETWEEN TINES : 0.15mm MAX.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	K.ASAKAWA	24JAN94		Tyco Electronics AMP K.K.	
CHK	S.KUBOUCHI	24JAN94		Kawasaki, Japan	
APVD	S.KUBOUCHI	7NOV97		NAME 名称	
PRODUCT SPEC 製品規格			2.0 A-F CONN. REC ASSEMBLY (V-TYPE WITH BOSS)		
APPLICATION SPEC 取付適用規格			SIZE	CAGE CODE	DRAWING NO 番号
WEIGHT			A3	00779	179395
CUSTOMER DRAWING			SCALE	NTS	SHEET 1 OF 1
			REV F		