




LOC		DIST		REV		DATE		BY		APP	
AV	IN	P	LYR	DESCRIPTION							
		1		FIRST DRAFT		07AUG2007		MBH		AV	
		2		REVISED - ADDED CUTOUTS TO SIDE WALLS		12JAN2009		MBH		AV	
		A		RELEASE		03APR2009		AV		AV	

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWG. HITCHCOCK		07AUG2007		NAME		13 POSITION (9-0.64 X 4-2.8) UNSEALED INTERFACE	
mm		0.001		A. VASRINDER		07AUG2007		PRODUCT SPEC		-	
0.001		0.001		APPLICATION SPEC		WEIGHT		SIZE		CAGE CODE	
0.001		0.001		CUSTOMER DRAWING		DRAWING NO		RESTRICTED TO		REV	
0.001		0.001		SCALE		6:1		SHEET		1 OF 2	
0.001		0.001		00779		1924667-INT		-		-	

- NOTES:
- KEYING OPTION "A" SHOWN IN GENERAL VIEWS.
 - 0.64 PINS: 0.8μm MIN TIN FOR A LENGTH OF 4.15 MIN FROM MATING END, OVER 2.0μm MIN NICKEL.
2.8 BLADES: 0.8μm MIN TIN FOR A LENGTH OF 6.2 MIN FROM MATING END, OVER 2.0μm MIN NICKEL.
 - DATUM SIZE TO BE MEASURED IN ZONE 1.
 - DATUM SIZE TO BE MEASURED IN ZONE 11.
 - DRAFT WITHIN TOLERANCE.
 - ALL UNMARKED RADII TO BE R0.3±0.1, UNLESS OTHERWISE SPECIFIED.
 - MATES WITH TE PART # 1924667

