



REVISIONS				
REV	DESCRIPTION	DATE	BY	APP'D
N2	ECR-23-192679	20MAR2024	JS	JS



ASSEMBLED VIEW



- △ CABLE CLAMP WILL ACCEPT 12.70 TO 25.40 [.500 TO 1.000] DIA CABLE (USE BUSHING 202038 OR 202039 FOR 12.70 [.500] DIA CABLE).
- △ ZINC PLATING WITH HEXAVALENT CHROMATE COATING.
- △ ZINC PLATING WITHOUT HEXAVALENT CHROMATE COATING.

△	71.04 [2.797]	1-202711-2
△	54.86 [2.160]	1-202711-1
△	71.04 [2.797]	202711-3
OBSELETE	54.86 [2.160]	202711-1
SCREW FINISH	L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN C. OBERMAN 22 AUG 96	APPROVED R. STONE 06 AUG 96	NAME G. STEINHÄUER 21 JAN 97	RESTRICTED TO
0. PLC ± -	1. PLC ± -	2. PLC ± -	3. PLC ± -	4. PLC ± -	ANGLES ± -
MATERIAL	FINISH	WEIGHT 0.000000	SIZE A1	CAGE CODE 00779	DRAWING NO. C=202711
CUSTOMER DRAWING		SCALE 2:1	SHEET 1 of 1	REV N2	

STE TE Connectivity

SHIELD KIT, UNASSEMBLED, 75 POSITION, 2 PIECE, M SERIES