





CHART A

FROM	PRIZM	COLOR
MTP® -1-1	PRIZM-1-1	BLUE
MTP® -1-2	PRIZM-1-2	ORANGE
MTP® -1-3	PRIZM-1-3	GREEN
MTP® -1-4	PRIZM-1-4	BROWN
MTP® -1-5	PRIZM-1-5	SLATE
MTP® -1-6	PRIZM-1-6	WHITE
MTP® -1-7	PRIZM-1-7	RED
MTP® -1-8	PRIZM-1-8	BLACK
MTP® -1-9	PRIZM-1-9	YELLOW
MTP® -1-10	PRIZM-1-10	VIOLET
MTP® -1-11	PRIZM-1-11	ROSE
MTP® -1-12	PRIZM-1-12	AQUA

1. MAXIMUM CABLE ASSEMBLY THROUGHPUT INSERTION LOSS PER CHANNEL IS 1.5dB AT 850nm. APERATURE LOSS MAX 5.15dB AT 850nm.


2. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702.

 SEE TRACE LABEL DETAIL.

4. MTP® ENDFACE GEOMETRY MUST MEET TE SPECIFICATION 115-1215-7: MAXIMUM CORE DIP

2123723-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.BRIGGS	02JAN2013	 TE Connectivity	
DIMENSIONS: METERS		CHK J.DAVIS	02JAN2013		
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.DAVIS	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC — APPLICATION SPEC —	
MATERIAL —		FINISH —		WEIGHT —	
CUSTOMER DRAWING				SCALE NTS	

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=2123723

RESTRICTED TO
—

SHEET
1 OF 1

REV
1